


# **Vice Jaw Set for Versagrip Clamps**







12037

## Material

Steel, hardened (52-54 HRc).

# **Technical Notes**

The Versagrip jaws increase the functionality of your 100 and 150mm vices. This is a simple bolt-on system that allows you to perform aggressive machining operations

whilst clamping on as little as 1,5mm for irregular shaped parts.

Ideal for small batch sizes or when building a fixture is not economical.

#### Tips

Has penetrating teeth designed to bite into your workpiece to prevent lateral and hori-

zontal movement. They will hold flame cut parts, castings and even parts with negative draft.

## **Important Notes**

Set includes a pair of vice jaws, and four Versagrip clamps, part no. 12036.W0175.

Order No.	For vice size	Туре	Jaw type	Vice jaw	Versagrip clamps	$d_1$	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	l <sub>1</sub>	$w_1$	Number of holes	Weight g
12037.W0015	4"/6"	Vice jaw set	With holes	2 off	4 pc 12036. W0175	98,55	63,5	47,75	23,87	17,47	150	25,4	7	2460
12037.W0020	6"	Vice jaw set	With holes	2 off	4 pc 12036. W0175	98,55		47,75	23,87		200	25,4	9	3470
12037.W0115		Vice jaw set	W/o holes	2 off	4 pc 12036. W0175			47,75			150	25,4	7	2780
12037.W0120		Vice jaw set	W/o holes	2 off	4 pc 12036. W0175			47,75			200	25,4	9	3640



