


Cam Latches - Flexi-System

tamper evident - for wire or cable tie - zinc







A1210

Material

Body & Insert: die cast zinc, bright chrome plated.

Supplied With: Nut: steel.

Not supplied: CAM - order separately.

Technical Notes

Order cam and key separately.

Cams: see suitable cam A0203, A0224 and

A0240. Select "without projection" cam

Dimensions ch and cl relate to cam. Use formula to calculate ch (required cam offset), and refer to cam selection chart;

ch = h - lh where;

ch = required cam off-set/height.

h = grip length (distance between inside of

latch face and front of cam).

lh = body length of cam latch/lock to be
used (see product table below).

Keys: see A0102.

Rods & Guides: to achieve 3-point latching

- A0303, A0321, A0325.

Tips

Quarter-turn opening or closing.

 Order No.
 a
 b
 lh

 A1210.AW0028
 28
 6.5
 20

