



**J0360**

DRAW LATCHES

**Material**

All parts from stainless steel, AISI 304, satin finish. Fixing screws not included.

Order No.	$l_1$	Load capacity kg	$h_1$	$w_1$	$\varnothing d_1$	$l_2$	$l_3$ 0 -0.5	$l_4$	$l_5$	$l_6$	$l_7$	$w_2$	$w_3$ $\pm 0.2$	$w_4$	Weight g
J0360.AC0030	82	80	19.5	33.6	4.3	38.5	30	13.5	5	5	52	32	13	25	111

