


Heavy Duty Soft-Opening Stays For downward opening lid, 90° opening angle

Soft & Spring Stays





N0420

Material

Arm: zinc alloy, steel, bright nickel finish. Body: plastic.

Technical Notes

For use with lids which are downward opening, with piano, butt or drop hinges. Designed to hold door in both closed and open position. Designed to control speed

at which a suitable lid opens, for smooth controlled motion. For use in pairs. Opening angle of 90°. Temperature range 0° to 40°C.

Important Notes

Improper application, or use on a lid not within recommended size and load bearing value, may lead to stay being overcome

and slamming of lid.

Application must be within both the min. and max. load bearing value, stays are for use in pairs see above table.

Check Load Bearing Value (T):

T (Load Bearing Value of stay Kg/cm) = 1/2 Door Height cm x Door Weight Kg

| Order No. | Туре | Acceptable load bearing pair | Hand | Weight |
|--------------|-------------|------------------------------|-------|--------|
| | | kg/cm | | g |
| | | min. max. | | |
| N0420.AC0020 | Light Duty | 140 to 200 | Left | 290 |
| N0420.AC0025 | Medium Duty | 200 to 250 | Left | 290 |
| N0420.AC0030 | Heavy Duty | 250 to 300 | Left | 310 |
| N0420.AC0120 | Light Duty | 140 to 200 | Right | 290 |
| N0420.AC0125 | Medium Duty | 200 to 250 | Right | 290 |
| N0420.AC0130 | Heavy Duty | 250 to 300 | right | 310 |

