



N0800

LID & DOOR STAYS

Material

Stainless steel, AISI 304, polished finish.

Technical Notes

Left or right hand specific, please refer to table. Holds lid in open position.

Order No.	Type	l_1	l_2	t	w_1	w_2	Load kg max.	Weight g
N0800.AC0010	Right	277	230	2.0	30	24	40	120
N0800.AC0020	Right	198	152	1.5	28	23	40	85
N0800.AC0030	Right	150	105	1.5	28	23	30	75
N0800.AC0110	Left	277	230	2.0	30	24	40	120
N0800.AC0120	Left	198	152	1.5	28	23	40	85
N0800.AC0130	Left	150	105	1.5	28	23	30	75

