



V0700

CAPS, PLUGS, MASKING AND INSERTS

Material

Polyethylene, black.

Important Notes

Sold subject to minimum pack quantity.

Order No.	Thread	A/F	c	d	h ₁	h ₂	h ₃
V0700.AC0451	M 4	7	6.9	9.0	7.5	8.3	3.5
V0700.AC0453	M 5	8	7.9	10.9	8.5	9.3	5.0
V0700.AC0455	M 6	10	9.8	12.9	12.0	13.0	6.0
V0700.AC0457	M 8	13	12.8	16.8	14.0	15.0	9.0
V0700.AC0459	M10	17	16.7	21.3	18.5	19.5	9.0
V0700.AC0461	M12	19	18.7	23.6	20.0	21.5	11.0
V0700.AC0463	M14	22	21.7	27.5	22.5	24.0	12.0
V0700.AC0465	M16	24	23.7	29.8	25.5	27.0	14.0
V0700.AC0467	M18	27	26.8	34.0	29.0	43.0	15.0
V0700.AC0469	M20	30	29.8	37.7	31.0	33.2	17.0
V0700.AC0471	M22	32	31.8	39.7	34.0	36.2	19.0
V0700.AC0473	M24	36	35.8	44.4	38.0	39.2	20.0
V0700.AC0475	M27	41	40.8	50.1	44.0	46.5	23.0
V0700.AC0477	M30	46	45.8	55.9	49.0	51.5	25.0
V0700.AC0479	M33	50	49.8	60.5	53.0	55.5	27.0
V0700.AC0481	M36	55	54.8	67.0	57.0	59.5	30.0
V0700.AC0483	M39	60	59.7	72.0	60.0	62.5	38.0
V0700.AC0485	M42	65	63.7	76.5	63.0	65.5	42.0
V0700.AC0487	M45	70	69.7	85.5	73.0	75.5	38.0
V0700.AC0489	M48	75	75.0	91.6	78.5	81.0	41.0
V0700.AC0491	M52	80	80.0	98.0	83.4	86.2	43.5
V0700.AC0493	M56	85	85.0	104.2	88.6	91.6	48.0
V0700.AC0495	M64	95	95.0	116.7	102.0	105.5	55.0