


Push To Close Paddle Latches pull to open - slam action - standard cylinder lock -





B4703

Material

B4703.AW0020

Body and Handle: steel, black powder coated.

Cylinder lock: die cast zinc, zinc plated.

Supplied with: Keys: two per lock. **Not Supplied:** Catch plate: please order separately.

Blank - No Lock

Technical Notes

Spring loaded, slam action handle. Installation via 72x56mm cut out.


Order No. Lock type
B4703.AW0010 Std. Cylinder







B4713



Material

Body and Handle: steel, black powder coated.

Cylinder lock: die cast zinc, zinc plated. **Supplied with:** Keys: two per lock. **Not Supplied:** Catch plate: please order separately.

Technical Notes

Stud fixing type has 4 off M 6 welded studs for rear mounting with M 6 nuts (not supplied).

Universal left/right. For use inside of cabinet gasket.


Tips

Order No.	Lock type	Туре	h
B4713.AW0010	Std. Cylinder	Latch	31.5
B4713.AW0020	Std. Cylinder	Latch	44.0
B4713.AW0030	Std. Cylinder	Latch	55.0
B4713.AW0040	Blank - No Lock	Latch	31.5



Push To Close Paddle Latches

pull to open - slam action - standard cylinder lock -





B4733

Material

Body and Handle: steel, black powder coated.

Cylinder lock: die cast zinc, zinc plated. **Supplied with:** Keys: two per lock. **Not Supplied:** Catch plate: please order

separately.

Technical Notes

Stud fixing type has 4 off M 6 welded studs for rear mounting with M 6 nuts (not supplied).

Tips


Order No.	Lock type	Type	h	I	w
B4733.AW0010	Std. Cylinder	Latch	30.5	127	101.5
B4733.AW0020	Std. Cylinder	Latch	43.0	127	101.5
B4733.AW0030	Std. Cylinder	Latch	54.0	127	101.5
B4733.AW0040	Blank - No Lock	Latch	30.5	127	101.5
B4733.AW0050	Blank - No Lock	Latch	43.0	127	101.5







B4750



Material

Body and Handle: stainless steel, AISI 304. Cylinder lock: die cast zinc, chrome plated. **Supplied with:** Keys: two per lock. **Not Supplied:** Catch plate: please order separately.

Technical Notes

Hole fixing type requires 4 off M 6 screws (not supplied) for front mounting.

Spring loaded, slam action handle.

Universal left/right. For use inside of cabinet gasket.

Tips

Order No.	Туре	h_1	I_1	w_1
B4750.AW0010	With Lock	22	140	90
B4750.AW0020	Blank - No Lock	22	140	90






Push To Close Paddle Latches

pull to open - slam action - stainless steel

Paddle Latches





B4752

Material

Body and Handle: stainless steel, AISI 304.

Technical Notes

Spring loaded, slam action handle. Fitting via mounting bracket. Without

secondary lock, for easy access.
Universal left/right. For use inside of cabinet gasket.

Catch plate B4752.AW0310 available as separate order item.


Tips

Order No.	h	The state of the s	W
B4752.AW0010	5	56	42





B4756



Material

Body and Handle: stainless steel, AISI 304, or zinc plated steel.

Cylinder lock: die cast zinc, chrome plated. **Supplied with:** Keys: two per lock. **Not Supplied:** Catch plate: please order separately.

Technical Notes

Spring loaded, slam action handle. Hole fixing type requires 4 off M 6 screws (not supplied) for front mounting. Universal left/right. For use inside of cabinet gasket.


Tips

Order No.	Lock type	Material	Key type	h_1	I_1	w_1
B4756.AW0010	Std. Cylinder	Steel	Keyed Alike	22	120	92.5
B4756.AW0020	Std. Cylinder	Stainless Steel	-	22	120	92.5



Push To Close Paddle Latches

pull to open - standard cylinder lock - stainless steel





B4758

Material

Body and Handle: stainless steel, AISI 303. Cylinder lock: die cast zinc, chrome plated. **Supplied with:** Keys: two per lock. **Not Supplied:** Catch plate: please order separately.

Technical Notes

Hole fixing type requires 4 off M 5 screws (not supplied) for front fixing.
Universal left/right. For use inside of cabinet gasket.

Tips

Order No.	Lock type	Type	Key type	d	I_1	l ₂	w_1	w_2
B4758.AW0010	Std. Cylinder	Latch	Keyed Alike	5.5	140	95	108	97
B4758.AW0020	Std. Cylinder	Latch	Keyed Alike	5.0	146	130	146	68




recessed handle - standard cylinder lock - poly-





B4800



Material

Body and Handle: Polyamide plastic (PA), black.

Cylinder lock: die cast zinc, chrome plated. **Supplied with:** Keys: two per lock.

Technical Notes

Easy snap on fix mounting. Make cut out in panel as shown, and simply push in handle, snap on clips will spring back to securely mount handle.

Attach multi-point latching rods (A0303) to achieve two-point latching of cupboards, cabinets or enclosures. Suitable for panel thickness 1 - 1.5mm.

Order No.

Lock type

Key type Keyed Alike Ī

w 88.5

B4800.AW0010

Std. Cylinder

88.5



Wixroyd Cam Latches

product selection charts

	Cylinder Profile	Body	Locking System	Use Cam Type	
		stic	5,510		
	Std. Cylinder Lock 40mm Euro Padlockable Insert Driver	Die-Cast Zinc Polyamide Plastic Stainless Steel Steel Aluminium		Inside Gasketing Outside Gasketing With Projection W/O Projection	
	Std. Cylinder 40mm Euro Padlockable Insert Driver	Die-Cast Zinc Polyamide Pla Stainless Steel Steel	Pating-point-point-point	e Ga ide G Proj	•
			9 5 5 5	Insid Outs With W/O	
B1450 - Swing	g Handles - (Cam Control - Sli	ding Cover		B4754 - P
	,				
	•				
7	Cams: A	 \0203, A0224, A0) 240 - Keys:	 Supplied	
B2450 - Swing	g Handles - I	Rod Control - Slic	ding Cover		B4756 - P
MA					•
	/				0
		Cams: N/A - Ke	vs: Supplied		
B4604 - Cam	Latch - Conc	ealed T-handle,		1 1	B4758 - P
	✓	✓	65	/	
	0				
B4703 - Push-to		ms: Supplied - Ke dle Latch - Pull-to		able	B4800 - T
	✓	/	1	1	
R4713 - Push-to	n-Close Pade	Cams: N/A - Ke			
D4713 Tush to	010301 441		o open		
G	/	/	1	1	
		Cams: N/A - Ke		1 1	
B4733 - Push-to	o-Close Pade	dle Latch - Pull-to	o-Open		
	1		1		
	·				
		Cams: N/A - Ke		1	
B4750 - Push-to	o-Close Pade	dle Latch - Pull-to	o-Open		
	/		7	1	
		Cams: N/A - Ke	vs: Supplied		
B4752 - Push-	to-Close Pa	ddle Latch - Pull-			
	1	✓	1	/	
		Come: N/A	voi Sumalia I		
		Cams: N/A - Ke	ys. Supplied		I

_							
1		Cylinder Profile	Body		Locking System	Use	Cam Type
The Frederick	B4754 - Push		Die-Cast Zinc Polyamide Plastic Stainless Steel - Steel Aluminium	P Rating	uad 1-point 2-point 3-point	Inside Gasketing Outside Gasketing	With Projection W/O Projection
	2.70.				- p		
,		√	1		√	1	
			Cams: N/A - Ke	eys:	Supplied		
	B4756 - Push	to-Close Pad	ldle Latch - Pull	-to-	Open		
		✓	√		√	1	
			Cams: N/A - Ke	eys:	Supplied		
	B4758 - Push	to-Close Pad	ldle Latch - Pull	-to-	Open		
		✓	✓		√	s	
			Cams: N/A - K	5//6.	Sunnlied	ı	
	P4900 Turist	to Class Bas	Idle Latch - Sna				
	D4000 - IWIST	-to-Close Pat	iuie Lateii - Siia	p-U	 	l	l
		1	1		1	1	
			Cams: N/A - Ke	eys:	Supplied		

ov-WB1450-A-T-WB4800-A-T-cam-latches-product-selection-chart-rnh-Updated -25-10-2022