


Vertical Acting Toggle Clamps black - open arm - horizontal base

Optical Measuring Toggle





40000.2

Material

Body: steel matt black.

Bushes: case hardened and pre-lubricated. Handle: plastic, black, oil resistant, ergonomic.

Supplied complete with matt black clamping screw (with rubber pad).

Technical Notes

For fastening to mounting plates, etc.

symbola/symbol* alternative angle through using the removable stop. Opening angle (symbola/symbol/symbola/symbol*) can be changed by pressing in a stop pin on the clamp body.

For optical analysis applications.

Tins

Designed specifically for clamping of parts during photometric measurement. Uniform

matt black surface prevents reflection, enabling easy "knocking-out" of the clamp during optical analysis of a component.

Order No.	Size	F ₁ kN	F ₂ kN	Clamping so	rew	h ₁	h ₂	h ₃	h ₄ min.	h ₄ max.	I_1	l ₂	l ₃	Weight g
40000.W0100	0	0.5	0.7	M 4x34,	5	81	18	8	-4.0	6.5	49	50	32	60
40000.W0101	1	0.6	1.1	M 5x38,0)	98	19	10	-3.7	1.6	61	58	39	105
40000.W0102	2	8.0	1.2	M 6x46,0)	140	23	12	-4.4	4.4	78	89	52	175
40000.W0103	3	1.2	2.5	M 8x63,0)	188	33	18	-2.8	7.0	112	112	79	410
Order No.	I_4	I ₅	l ₆	I ₇	l ₈	l ₉	w_1	W_2		w_3	w_4	d_1	α	α^*
40000.W0100	14	5.5	22	8,5-13,5	5.5	-	4	32		23.0	-	4.5	95°	-
40000.W0101	18	6.0	27	16.0	5.5	-	5	34	22	,5-26,0	-	4.5	95°	-
40000.W0102	25	11.0	32	20.0	6.0	12.5	6	43	23	,0-31,0	27	5.5	105°	60°
40000.W0103	36	19.0	35	20.0	7.5	-	8	46		32.5	-	7.5	105°	60°




Vertical Acting Toggle Clamps

black - safety lever - open arm - horizontal base





40010.2



Material

Body: steel matt black.

Bushes: case hardened and pre-lubricated. Ergonomic soft feel, oil-resistant handle with large grip area.

Supplied complete with clamping screw (with rubber pad).

Technical Notes

The safety lever holds the clamping arm in

both the clamped and open position. This prevents opening under vibration or accidental movement of the clamping arm during assembly/disassembly of the fixture.

Opening angle (symbola/symbol/symbola/ symbol*) can be changed by pressing in a stop pin on the clamp body.

For optical analysis applications.

Tips


Order No.	Size	F ₁ kN	F ₂ kN	Clamping screw	h_1	h ₂	h ₃	h ₄ min.	h ₄ max.	I_1	I ₂	l ₃	Weight
40010.W0005	2	1.0	1.2	M 6x46	139	23	12	-4.4	4.4	78	88	52	260
Order No.	14	I ₅	I ₆	I ₇	l ₈	l ₉	w_1	W_2	w ₃		d_1	α	α*
40010.W0005	26	11	32	20	6	12.5	6	43	23-3	1	5.5	105°	60°





Vertical Acting Toggle Clamps open arm - vertical base - black

Optical Measuring Toggle





40050.2

Material

Body: steel matt black. Bushes: case hardened and pre-lubricated. Ergonomic soft feel, oil-resistant handle with large grip area.

Supplied complete with clamping screw (with rubber pad).

Technical Notes

For fastening to mounting plates, etc. Opening angle (symbola/symbol/symbola/ symbol*) can be changed by pressing in a stop pin on the clamp body.

For optical analysis applications.

Tips

Order No.	Size	F ₁ kN	F ₂ kN	Clamping s	crew	h_1	h ₂	h ₃	h ₄ min.	h ₄ max.	h ₅	h ₆	I_1	Weight g
40050.W0101	1	0.6	1.1	M 5x38	8	110.5	29	10	6.8	12	23,5-25,0	-	61	105
40050.W0102	2	8.0	1.2	M 6x4	6	114.5	38	12	10.5	19	28,5-32,0	30	78	175
40050.W0103	3	1.2	2.5	M 8x63	3	201.0	48	18	11.4	21	41.0	-	112	410
Order No.	l ₂	l ₃	I ₄	I ₅	I ₆	I ₇	I ₈	l ₉	\mathbf{w}_1	W_2	w_3	d_1	α	α*
40050.W0101	58	39	18	6	27	16	5.5	-	5	19	5	4.5	95°	-
40050.W0102	80	52	25	11	32	20	6.0	12.5	6	21	5	5.5	105°	60°
40050.W0103	113	79	36	19	40	20	7.5	-	8	27	6	7.5	105°	60°




Horizontal Acting Toggle Clamps black - open arm - vertical base - safety lever





40060.2



Material

Body: steel matt black.

Bushes: case hardened and pre-lubricated. Ergonomic soft feel, oil-resistant handle with large grip area.

Supplied complete with clamping screw (with rubber pad).

Technical Notes

For fastening to mounting plates, etc. Opening angle (symbola/symbol/symbola/ symbol*) can be changed by pressing in a stop pin on the clamp body.

For optical analysis applications.

Tips


Order No.	Size	F ₁ kN	F ₂ kN	Clamping screw	h_1	h ₂	h ₃	h ₄ min.	h ₄ max.	h ₅	I_1	l ₂	Weight
40060.W0006				M 8x63		48		16.5			112	114	470
Order No.	l ₃	I ₄	I ₅	I ₆	I ₇	l ₈	w_1	w_2	w ₃	3	d_1	α	α*
40060.W0006	79	37	19	40	7.5	20	8	45.5	6		7.5	105°	60°





Horizontal Acting Toggle Clamps black - open arm - horizontal base

Optical Measuring Toggle





41000.2

Material

Body: steel matt black. Bushes: case hardened and pre-lubricated. Ergonomic soft feel, oil-resistant handle with large grip area.

Supplied complete with clamping screw

(with rubber pad).

Technical Notes

For optical analysis applications.

Tips

Designed specifically for clamping of parts

during photometric measurement. Uniform matt black surface prevents reflection, enabling easy "knocking-out" of the clamp during optical analysis of a component.

41000.W0101 1 0.8 1.1 M 5x38,0 30.0 49.0 19.0 10.0 -3.6 1.8 120 42 10 41000.W0102 2 1.0 1.2 M 6x46,0 45.0 66.3 24.0 13.2 -2.6 5.0 162 64 18	. Weight g
41000.W0102 2 1.0 1.2 M 6x46,0 45.0 66.3 24.0 13.2 -2.6 5.0 162 64 18	35
,	2 105
41000.W0103 3 1.8 2.5 M 8x63,0 48.5 86.0 32.0 15.0 -7.4 5.0 206 73 32	4 185
	3 320
Order No. I_3 I_4 I_5 I_6 I_7 I_8 W_1 W_2 W_3 W_4 d_1 d_2 d_3	d_2 α
41000.W0100 9.0 5.5 25.5 11,5-15,5 6.25 - 25.0 4 16.0 - 4.6 - 90	- 90°
41000.W0101 18.8 8.0 34.0 13,0-14,5 5.50 - 34.0 5 18,0-21,5 - 5.2 - 96	- 90°
41000.W0102 32.0 16.0 38.0 26.0 6.00 12.7 42.0 6 19,5-29,5 28.5 5.6 5.6 90	5.6 90°
41000.W0103 37.0 14.0 50.0 25.7 7.00 - 45.5 8 22,0-31,8 31.6 6.5 5.1 96	- 1 000




Horizontal Acting Toggle Clamps black - open arm - vertical base





41050.2



Material

Body: steel, matt black.

Bushes: sizes 2-3 case hardened and prelubricated.

Ergonomic soft feel, oil-resistant handle with large grip area.

Supplied complete with clamping screw

(with rubber pad).

Technical Notes

Opening angle (symbola/symbol/symbola/ symbol*) can be changed by pressing in a stop pin on the clamp body.

For optical analysis applications.

Tips

Order No.	Size	F ₁	F ₂ C	Clamping screw	h_1	h ₂	h ₃	h ₄	h ₅ min.	h ₅	I_1	l ₂	I ₃	Weight g
41050.W0100	0	0.3	0.4	M 4x34.5	33	34	24.5	7.5	2.2	13.7	79.0	28.0	9.0	35
41050.W0101	1	0.8	1.1	M 5x38,0	43	49	31.5	10.0	8.9	14.8	119.7	41.7	18.5	105
41050.W0102	2	1.0	1.2	M 6x46,0	61	68	40.0	13.2	14.0	22.0	164.0	64.0	32.0	185
41050.W0103	3	1.8	2.5	M 8x63,0	65	86	49.0	15.0	9.5	22.0	206.0	73.0	39.0	320
Order No.	I_4	l ₅	I ₆	l ₇	l ₈	w_1	W_2	w_3	W_4	,	w ₅	d_1	d_2	α
41050.W0100	5.5	25.5	11,5-15	5,5 6.25	-	4	12	3	-	2	0.0	4.6	-	90°
41050.W0101	8.0	34.0	13,0-15	5,5 5.50	-	5	18	5	24.5	23,5	5-25,5	5.2	-	90°
41050.W0102	16.0	38.0	26.0	6.00	12.7	6	21	5	34.0	29,5	5-34,0	5.6	5.6	90°
41050.W0103	12.0	50.0	25.7	7.00	13.0	8	27	6	42.0	37,5	5-42,5	6.5	5.1	90°






Horizontal Acting Toggle Clamps

black - open arm - vertical base - safety

Optical Measuring Toggle





41060.2

Material

Body: steel, matt black.
Bushes: case hardened and pre-lubricated.
Ergonomic soft feel, oil-resistant handle
with large grip area.
Supplied complete with clamping screw.

Supplied complete with clamping screw (with rubber pad).

Technical Notes

The safety lever holds the clamp in both

the open and the closed position. This prevents opening under vibration or inadvertent movement of the clamping arm when loading or unloading a fixture. For optical analysis applications.

Tips

Designed specifically for clamping of parts during photometric measurement. Uniform matt black surface prevents reflection, enabling easy "knocking-out" of the clamp during optical analysis of a component.

Order No.	Size	F ₁	F ₂ kN	Clamping screv	w h ₁	h ₂	h ₃	h ₄	h ₅ min.	h ₅ max.	I_1	I_2	l ₃	Weight
41060.W0100	3	1.8		M 8x63	65	86	49	15			206	73	37	390
Order No.	I ₄	I ₅	I ₆	I ₇	l ₈	w_1	W_2	w_3	w_4	W	' 5	d_1	d_2	α
41060.W0100	14	50	25.7	7 7	13	8	47	6	42	38-	-42	6.5	5.1	90°




Horizontal Acting Toggle Clamps

black - open arm - vertical base





41062.1



Material

Body: steel, matt black. Bushes: case hardened and pre-lubricated. Ergonomic soft feel, oil-resistant handle with large grip area.

Supplied complete with clamping screw (with rubber pad).

Technical Notes

symbola/symbol* alternative angle

through using the removable stop.

Opening angle (symbola/symbol/symbola/symbol*) can be changed by pressing in a stop pin on the clamp body.

For optical analysis applications.

Tips

Designed specifically for clamping of parts during photometric measurement. Uniform matt black surface prevents reflection, enabling easy "knocking-out" of the clamp during optical analysis of a component.


Order No.	Size	F ₁ kN	F ₂ kN	h_1	h ₂	h ₃	h ₄	I_1	l ₂	l ₃	I ₄	I ₅	Weight
41062.W0100	2	1	1.2	190	34	67	13.2	173.5	64	38.6	11	38	61
Order No.	16	I ₇	I ₈		w_1	w_2	w_3	w_4	W	5	d_1	d_2	α
41062.W0100	26	6	13.	1	6.2	21	5	27	23-2	28	5.6	4.8	90°





Horizontal Acting Toggle Clamps black - open arm - vertical base

Optical Measuring Toggle





41062.2

Material

Body: steel, matt black. Bushes: case hardened and pre-lubricated. Ergonomic soft feel, oil-resistant handle with large grip area.

Supplied complete with clamping screw

(with rubber pad).

Technical Notes

For optical analysis applications.

Tips

Designed specifically for clamping of parts

during photometric measurement. Uniform matt black surface prevents reflection, enabling easy "knocking-out" of the clamp during optical analysis of a component.

Order No.	Size	F ₁ kN	F ₂	h_1	h ₂	h ₃	h ₄	I_1	l ₂	l ₃	I ₄	I ₅	Weight
41062.W0110			2.5				15						320
Order No.	I ₆	I ₇	l ₈	w_1		w ₂	w_3	W_4	W	5	d_1	d_2	α
41062.W0110	25.7	7	13	8		27	6	27	22,5-2	27,5	6.5	5.1	90°




Horizontal Acting Toggle Clamps

black - open arm - vertical base - safety





41064.1



Material

Body: steel, matt black.

Bushes: case hardened and pre-lubricated. Ergonomic soft feel, oil-resistant handle with large grip area.

Supplied complete with clamping screw (with rubber pad).

Technical Notes

The safety lever holds the clamping arm in

both the clamped and open position. This prevents opening under vibration or accidental movement of the clamping arm during assembly/disassembly of the fixture.

For optical analysis applications.

Tinc

Designed specifically for clamping of parts during photometric measurement. Uniform

matt black surface prevents reflection, enabling easy "knocking-out" of the clamp during optical analysis of a component.

Order No.	Size	$F_1^{}$ kN	F ₂ kN	h_1	h_2	h ₃	h ₄	I_1	l ₂	l ₃	I ₄	I ₅	Weight
41064.W0100	2	1	1.2	61	67	34	13.2	173.5	64	38.6	11	38	230
Order No.	l ₆	I ₇	I ₈		w_1	w_2	w_3	W_4	W	5	d_1	d_2	α
41064.W0100	26	6	13.1		6.2	48	5	27	23-	28	5.6	4.8	90°






Horizontal Acting Toggle Clamps

black - open arm - vertical base - safety

Optical Measuring Toggle





41064.2

Material

Body: steel, matt black. Bushes: case hardened and pre-lubricated. Ergonomic soft feel, oil-resistant handle with large grip area.

Supplied complete with clamping screw (with rubber pad).

Technical Notes

The safety lever holds the clamping arm in

both the clamped and open position. This prevents opening under vibration or accidental movement of the clamping arm during assembly/disassembly of the fixture.

For optical analysis applications.

Tinc

Designed specifically for clamping of parts during photometric measurement. Uniform

matt black surface prevents reflection, enabling easy "knocking-out" of the clamp during optical analysis of a component.

Order No.	Size	F ₁ kN	F ₂ kN	h_1	h ₂	h ₃	h ₄	I_1	l ₂	I ₃	l ₄	I ₅	Weight
41064.W0110	3	1.8	2.5	65	86	34	15	206	73	34.5	16.5	50	350
Order No.	I ₆	I ₇	I ₈	w_1		w ₂	w ₃	W_4	W	5	d_1	d_2	α
41064.W0110	25.7	7	13	8	4	16.5	6	27	22,5-	27,5	6.5	5.1	90°




Push-Pull Type Toggle Clamps - Black

for optical measuring equipment





42000.2



Material

Body: steel, matt black. Bushes: case hardened and pre-lubricated. Ergonomic soft feel, oil-resistant handle with large grip area.

Supplied complete with clamping screw

45020.2 (with rubber pad).

Technical Notes

For optical analysis applications.

Tips

Designed specifically for clamping of parts


during photometric measurement. Uniform matt black surface prevents reflection, enabling easy "knocking-out" of the clamp during optical analysis of a component.

Order No.	Size	F ₁ kN	F ₂ kN	Stroke s ₁	d_1	d_2	Clamping screw d ₃	d ₄	h_1	h ₂	I_1	Weight g
42000.W0501	1	1	1	20	M12x1,5	8	M 4x20	4.5	60	15	91	125
42000.W0502	2	2	2	26	M16x1,5	10	M 6x25	5.6	95	20	114	245
Order No.	I ₂		l ₃ min.	l ₄ min.	I ₅		I ₆ I ₇	l ₈		w_1		w ₂
42000.W0501 42000.W0502	72 105		24.5 32.5	12 17	20 34		20 16 25 19	7.0 12.5		30 50	,	0-19,5 3-36,0



Push-Pull Type Toggle Clamps - Black for optical measuring equipment

Optical Measuring Toggle





42050.2

Material

Body: malleable cast iron, matt black. Levers and rods of tempered steel, matt black galvanised.

Technical Notes

For optical analysis applications.

Tips

Order No.	Size	F ₁	Clamping screw	Weight
42050.W0103	2	kN	M 8x44	g 540
4ZUDU.WUTUD	.)	4	IVI 0X44	:)40

