



9802



Technical Notes

For guidance on selection of most suitable insert, please refer to Application Table.

Tips

Inserts, housings and handles can be bought separately creating a flexible easy to use modular mallet system. For full range of inserts see part 9800.

Important Notes

Soft metal inserts no. 9800.W788 must not be used in light alloy housing no. 9802.

Simplex Mallets

with light alloy housing and wooden handle



Order No.	Insert type	Head Ø			 g
9802.W130	TPE - soft blue	30	90	300	180
9802.W140	TPE - soft blue	40	110	330	380
9802.W150	TPE - soft blue	50	135	350	640
9802.W160	TPE - soft blue	60	145	405	880
9802.W230	TPE - rubber	30	90	300	280
9802.W240	TPE - rubber	40	110	330	350
9802.W250	TPE - rubber	50	135	350	610
9802.W260	TPE - rubber	60	145	405	860
9802.W330	TPE - mid grey	30	90	300	200
9802.W340	TPE - mid grey	40	110	330	380
9802.W350	TPE - mid grey	50	135	350	620
9802.W360	TPE - mid grey	60	145	405	860
9802.W430	Plastic - red	30	90	300	190
9802.W440	Plastic - red	40	110	330	370
9802.W450	Plastic - red	50	135	350	620
9802.W460	Plastic - red	60	145	405	830
9802.W530	Super plastic - white	30	90	300	180
9802.W540	Super plastic - white	40	110	330	380
9802.W550	Super plastic - white	50	135	350	580
9802.W560	Super plastic - white	60	145	405	790
9802.W630	Nylon - white	30	90	300	190
9802.W640	Nylon - white	40	110	330	370
9802.W650	Nylon - white	50	135	350	615
9802.W660	Nylon - white	60	145	405	850

HAND TOOLS

