



12550.6

ADJUSTABLE VERTICAL CLAMPS

Material

Steel (C45), black oxide finish, tempered - 12550.W3100 and 12550.W3120).

Technical Notes

For use with hook clamps part no's 12550. W0010- .W0012 and 12554.

Order No.	Hook clamp size dia.	h_1	l_1	d_1	d_2 tol. f7	h_2	d_3	l_2	w_1	w_2	w_3	Weight g
12550.W3100	10	6	-	14	$10^{+0,1}$	16	4,3 (M 4)	14	34	24	-	20
12550.W3120	12	8	-	16	$12^{+0,1}$	19	5,3 (M 5)	16	40	28	-	30
12550.W3180	18	10	11.3	24	18	25	6,6 (M 6)	24	50	38	15	85
12550.W3200	20	12	13.4	28	20	30	9,0 (M 8)	28	60	45	20	150
12550.W3250	25	14	15.0	35	25	40	11,0 (M10)	35	75	55	20	290
12550.W3320	32	16	20.2	42	32	40	13,0 (M12)	41	85	65	25	400

