



15374.1

SCREW JACKS

Material

Steel, tempered, plasma-nitrided and burnished.

Technical Notes

Interchangeable top bearing for the fine

thread modular screw jack 15537.2.

Compensation of large work-piece tolerances.

For use in horizontal and vertical clamping.

Order No.	Bearing type	h_1	d_1	d_2	r_1	Weight g
15374.W0075	Spherical	24.7	75	20.5	140	655
15374.W0175	Smooth	24.7	75	20.5	140	739
15374.W0275	Point	24.7	75	20.5	140	651



With the modular screw jack your production becomes even more flexible and economical. When combined you can achieve a maximum height of 1620mm.

Benefits

- Maximum height of 1620mm.
- Quick set-up time.

The Elements

- 1 Bearing pads, 15374.W0075, 15374.W0175, 15374.W0275
- 2 Screw jack, 15370.W0040, 15372.W0023
- 3 Spacer, 15370.W0116, 15370.W0126, 15370.W0135
- 4 Base, 15370.W0236, 15370.W0356, 15370.W0456
- 5 Thread adapter, 15374.W0016, 15374.W0020, 15374.W0024

