



Clamping Sets with low height clamps 12200

Standard Manual Clam-



19100

STANDARD MANUAL CLAMPING

Material

Clamp sets are designed for use on T-slot machines, and contain all the necessary

parts to quickly clamp tools, fixtures or workpieces. All parts are interchangeable and are made of heat treated steel to DIN

standard (class 8 or class 10). The clamping set comes in a wooden box which has a removable lid.

Order No.	Thread & Slot size	Box l x w x h	Step blocks 14000	T-Bolts 21000	Step clamps 10020	Studs 21100	Weight kg
19100.W0010	M10 x 10	355x270x47	.W0001 x 4pcs .W0002 x 4pcs .W0003 x 2pcs	40mm .W0101 x 2pcs 63mm .W0102 x 4pcs 100mm .W0103 x 4pcs	.W0010 x 4pcs	80mm .W0102 x 4pcs	9.2
19100.W0012	M12 x 12	460x330x50	.W0002 x 4pcs .W0003 x 4pcs	50mm .W0121 x 2pcs 80mm .W0123 x 4pcs 125mm .W0124 x 4pcs	.W0014 x 4pcs	100mm .W0124 x 4pcs	14.3
19100.W0014	M12 x 14	460x330x50	.W0002 x 4pcs .W0003 x 4pcs	50mm .W0141 x 2pcs 80mm .W0143 x 4pcs 125mm .W0144 x 4pcs	.W0014 x 4pcs	100mm .W0124 x 4pcs	14.6
19100.W0015	M14 x 16	510x415x50	.W0002 x 4pcs .W0003 x 4pcs	63mm .W0161 x 2pcs 100mm .W0162 x 4pcs 160mm .W0163 x 4pcs	.W0018 x 4pcs	125mm .W0147 x 4pcs	18.5
19100.W0016	M16 x 16	510x415x50	.W0002 x 4pcs .W0003 x 4pcs	63mm .W0165 x 2pcs 100mm .W0167 x 4pcs 160mm .W0168 x 4pcs	.W0018 x 4pcs	125mm .W0164 x 4pcs	21.5
19100.W0018	M16 x 18	510x415x50	.W0002 x 4pcs .W0003 x 4pcs	63mm .W0181 x 2pcs 100mm .W0183 x 4pcs 160mm .W0184 x 4pcs	.W0018 x 4pcs	125mm .W0164 x 4pcs	21500

Order No.	Fixture nuts 24300	Extension nuts 24600	Dished washers 25700	Low height clamp 12200	T-Slot scrapper 26300	Spanner	Thread paste
19100.W0010	.W0110 x 6pcs	.W0110 x 4pcs	.W0110 x 6pcs	.W0012 x 4pcs	-	16 x 1pc	1pc



Order No.	Fixture nuts 24300	Extension nuts 24600	Dished washers 25700	Low height clamp 12200	T-Slot scrapper 26300	Spanner	Thread paste
19100.W0012	.W0112 x 6pcs	.W0112 x 4pcs	.W0112 x 6pcs	.W0012 x 4pcs	-	18 x 1pc	1pc
19100.W0014	.W0112 x 6pcs	.W0112 x 4pcs	.W0112 x 6pcs	.W0014 x 4pcs	.W0120 x 1pc	18 x 1pc	1pc
19100.W0015	.W0114 x 6pcs	.W0114 x 4pcs	.W0114 x 6pcs	.W0016 x 1pc	.W0120 x 1pc	22 x 1pc	1pc
19100.W0016	.W0116 x 6pcs	.W0116 x 4pcs	.W0116 x 6pcs	.W0016 x 1pc	.W0120 x 1pc	24 x 1pc	1pc
19100.W0018	.W0116 x 6pcs	.W0116 x 4pcs	.W0116 x 6pcs	.W0018 x 1pc	.W0120 x 1pc	24 x 1pc	1pc