



Clamping Sets with stop clamps 10020

Standard Manual Clam-



19200

STANDARD MANUAL CLAMPING

Technical Notes

High quality clamping set for machines.
Comprising step clamps no. 10200 and

step blocks no. 14000. High quality T-bolts
and studs (class 8 or class 10). With spring
clamp supports.

Order No.	Thread & Slot size	Box l x w x h	Step blocks 14000	T-Bolts 21000	Step clamps 10020	Studs 21100	Weight kg
19200.W0010	M10 x 10	355x225x47	.W0001 x 4pcs .W0002 x 4pcs .W0003 x 2pcs	63mm .W0102 x 4pcs 100mm .W0103 x 4pcs	.W0011 x 4pcs	80mm .W0083 x 4pcs	6.5
19200.W0012	M12 x 12	359x333x52	.W0002 x 4pcs .W0003 x 4pcs	80mm .W0123 x 4pcs 125mm .W0124 x 4pcs	.W0014 x 4pcs	100mm .W0124 x 4pcs	11.0
19200.W0014	M12 x 14	359x333x52	.W0002 x 4pcs .W0003 x 4pcs	80mm .W0123 x 4pcs 125mm .W0124 x 4pcs	.W0014 x 4pcs	100mm .W0124 x 4pcs	11.1
19200.W0016	M16 x 16	390x415x55	.W0002 x 4pcs .W0003 x 4pcs	100mm .W0167 x 4pcs 160mm .W0168 x 4pcs	.W0018 x 4pcs	125mm .W0164 x 4pcs	16.5
19200.W0018	M16 x 18	390x415x55	.W0002 x 4pcs .W0003 x 4pcs	100mm .W0183 x 4pcs 160mm .W0184 x 4pcs	.W0018 x 4pcs	125mm .W0164 x 4pcs	16.5
19200.W0020	M20 x 20	480x528x60	.W0002 x 4pcs .W0003 x 4pcs	125mm .W0203 x 4pcs 200mm .W0205 x 4pcs	.W0022 x 4pcs	125mm .W0202 x 4pcs	24.5
19200.W0022	M20 x 22	480x528x60	.W0002 x 4pcs .W0003 x 4pcs	125mm .W0223 x 4pcs 200mm .W0225 x 4pcs	.W0022 x 4pcs	125mm .W0202 x 4pcs	24.5
19200.W0024	M20 x 24	480x528x60	.W0002 x 4pcs .W0003 x 4pcs	-	.W0022 x 4pcs	125mm .W0202 x 8pcs 200mm .W0204 x 4pcs	24.8



Order No.	T-nuts 24000	Fixture nuts 24300	Extension nuts 24600	Dished washers 25700	T-Slot scrappier 26300	Clamp Support 26000	Span ner	Thread paste
19200.W0010	-	.W0110 x 6pcs	.W0110 x 4pcs	.W0110 x 6pcs	-	.W0101 x 4pcs	16 x 1pc	1pc
19200.W0012	-	.W0112 x 4pcs	.W0112 x 4pcs	.W0112 x 6pcs	-	.W0102 x 4pcs	18 x 1pc	1pc
19200.W0014	-	.W0112 x 4pcs	.W0112 x 4pcs	.W0112 x 6pcs	.W0120 x 1pc	.W0102 x 4pcs	18 x 1pc	1pc
19200.W0016	-	.W0116 x 4pcs	.W0116 x 4pcs	.W0116 x 6pcs	.W0120 x 1pc	.W0103 x 4pcs	24 x 1pc	1pc
19200.W0018	-	.W0116 x 4pcs	.W0116 x 4pcs	.W0116 x 6pcs	.W0120 x 1pc	.W0103 x 4pcs	24 x 1pc	1pc
19200.W0020	-	.W0120 x 6pcs	.W0120 x 4pcs	.W0120 x 6pcs	.W0120 x 1pc	.W0104 x 4pcs	30 x 1pc	1pc
19200.W0022	-	.W0120 x 6pcs	.W0120 x 4pcs	.W0120 x 6pcs	.W0132 x 1pc	.W0104 x 4pcs	30 x 1pc	1pc
19200.W0024	.W0242 x 8pcs	.W0120 x 6pcs	.W0120 x 4pcs	.W0120 x 6pcs	.W0132 x 1pc	.W0104 x 4pcs	30 x 1pc	1pc