



32700

INDEX PLUNGER & PINS

Material

Free cutting steel type-

Body: free cutting steel, blackened.

Pin: steel, hardened.

Grip: thermoplastic PA6, black.

Stainless steel type -

Body: stainless steel 1.4305 (AISI 303).

Pin: stainless steel 1.4305 (AISI 303),

nickel plated.

Grip: thermoplastic PA6, black.

Technical Notes

„Non Locking“ type- pin simply springs back when pull ring released.

Thread recess on body allows full engagement of thread length. Hexagon collar improves leverage for secure installation. Without grip temperature resistance up to 250°C .

Distance collars no. 32750 can be used to adapt screw length.

Lock nuts sold separately See Products 65690 and 65692

Tips

Grip non-removable.

Spring loads * = statistical average.

Order No.	Type	Material	d ₁ -0.02 -0.04	d ₂	d ₃	d ₄	l ₁ ≈	l ₂ min.	l ₃	l ₄	l ₅	l ₆ min.	A/F	Spring load	Spring load	Weight g
														F ₁ N ≈	F ₂ N ≈	
32700.W0005	With Grip	Steel	5	M10x1,0	21		45,0	5	17	5		15	12	6,0	14	19,0
32700.W0006	With Grip	Steel	6	M12x1,5	25		54,5	6	20	6		17	14	5,5	13	31,0
32700.W0008	With Grip	Steel	8	M16x1,5	31		69,0	8	26	8		23	19	11,5	28	71,0
32700.W0010	With Grip	Steel	10	M20x1,5	31		80,0	10	33	10		30	22	23,0	54	115,0
32700.W0025	No Grip	Steel	5	M10x1,0		M 5		5	17	5	6	15	12	6,0	14	14,0
32700.W0026	No Grip	Steel	6	M12x1,5		M 6		6	20	6	10	17	14	5,5	13	23,0
32700.W0028	No Grip	Steel	8	M16x1,5		M 8		8	26	8	12	23	19	11,5	28	54,0
32700.W0030	No Grip	Steel	10	M20x1,5		M 8		10	33	10	12	30	22	23,0	54	79,0
32700.W0405	With Grip	Stainless	5	M10x1,0	21		45,0	5	17	5		15	12	6,0	14	19,0
32700.W0406	With Grip	Stainless	6	M12x1,5	25		54,5	6	20	6		17	14	5,5	13	31,0
32700.W0408	With Grip	Stainless	8	M16x1,5	31		69,0	8	26	8		23	19	11,5	28	71,0
32700.W0410	With Grip	Stainless	10	M20x1,5	31		80,0	10	33	10		30	22	23,0	54	115,0
32700.W0425	No Grip	Stainless	5	M10x1,0		M 5		5	17	5	6	15	12	6,0	14	14,0
32700.W0426	No Grip	Stainless	6	M12x1,5		M 6		6	20	6	10	17	14	5,5	13	23,0
32700.W0428	No Grip	Stainless	8	M16x1,5		M 8		8	26	8	12	23	19	11,5	28	54,0
32700.W0430	No Grip	Stainless	10	M20x1,5		M 8		10	33	10	12	30	22	23,0	54	79,0