


One-Touch Fastener - Ball Clamping



33930



Material

Body: steel, nickel plated.

Technical Notes


One-touch fasteners are the ideal solution for applications requiring rapid and recurring change over of tooling or set ups. Use in applications as diverse as bottling processes, machine covers, changing of cogs and drive belts. One-touch fasteners provide a quick, simple and secure change over solution - no time waste in unfastening screws or other permanent fixings, and no opportunity for lost fixings in your machinery.

Important Notes

Pin 33930 is for use inconjunction with

one-touch fasteners, ball clamping; 33934 and 33936. Suitable for panels/enclosures of 6 to 20 mm thickness. Requires an M 6 thread, 6mm deep for installation into blind hole. See technical pages for further information.

Order No.	d ₁ -0.2 -0.4	h_1	h ₂	h ₃	m	A/F	Weight
33930.W0008	Ø8	23	5	4	M 5x0,8	6	7







ov-W33910-A-T-W33956-A-T-one-touch-fasteners-a-lnh - Updated - 27-10-2022

One-Touch Fasteners - Alternatives to Screws









Easy & Secure! For Quick Changeover with No Tools!























One-Touch Fasteners

quick-easy-secure




One-Touch Change Over







Installation and Removal of Rotary Blades and **Changes of Shooters**



Changes of Star Wheels and Guide Plates





Changes of Pusher and Changes of Chuck **Handling Machines**



ov-W33910-A-T-W33956-A-T-one-touch-fasteners-b-rnh - Updated - 27-10-2022