



Material

Steel body with silver zinc plated thread.
Synthetic rubber pad (65-70 Shore A) with anti-slide cavity.

Technical Notes

Suitable for machinery with low frequency vibrations and for irregular floors.

Order No.	d_1	h	d_2	l	Load range Kgf
34900.W0048	48	23	M 8	40	0-80
34900.W0060	60	25	M10	83	50-120
34900.W0075	75	30	M12	90	80-150
34900.W0090	90	33	M12	90	120-300
34900.W0105	105	38	M16	110	250-500
34900.W0125	125	45	M16	110	400-800
34900.W0150	150	55	M16	110	600-1000
34900.W0170	170	57	M16	110	1000-1600
34900.W0187	187	70	M20	115	1400-2400
34900.W0210	210	75	M20	115	2000-3500