



61620

ANTI-VIBRATION

Material

Rubber on silver zinc plated steel (rubber hardness - 60Shore A).

can be drilled to suit the number of threads, thread sizes and the pitch you require. Other sizes can be supplied on request. Suitable for very heavy loads.

Technical Notes

The metal plates are provided blank so they

| Order No. | l_1 | w_1 | h_1 | h_2 | h_3 | Axial load kgf max. |
|-------------|-------|-------|-------|-------|-------|---------------------------|
| 61620.W0040 | 550 | 40 | 40 | 24 | 8 | 2200 |
| 61620.W0050 | 515 | 50 | 40 | 20 | 10 | 2800 |
| 61620.W0051 | 515 | 50 | 50 | 30 | 10 | 2570 |
| 61620.W0060 | 650 | 60 | 50 | 30 | 10 | 3900 |
| 61620.W0061 | 650 | 60 | 60 | 40 | 10 | 3500 |
| 61620.W0070 | 600 | 70 | 50 | 30 | 10 | 4200 |
| 61620.W0171 | 600 | 70 | 55 | 35 | 10 | 4000 |
| 61620.W0180 | 600 | 80 | 80 | 50 | 15 | 4320 |
| 61620.W0100 | 415 | 100 | 60 | 30 | 15 | 4150 |
| 61620.W0101 | 415 | 100 | 80 | 50 | 15 | 3740 |
| 61620.W0150 | 500 | 150 | 80 | 50 | 15 | 6750 |