



61830

ANTI-VIBRATION

Material

Rubber (hardness - 55 Shore A).

Technical Notes

Used in a wide range of vibrating

machines.

Allows high deformation with excellent spring back characteristics.

Supports axial and radial loads but not

designed for traction or tension loads. For radial loads please contact our Technical Department.

Order No.	d ₁	h ₁	d ₂	d ₃	Compression max.	Axial load kgf max.
61830.W0001	95	88	23	30	28	200
61830.W0002	100	110	20	30	36	500
61830.W0004	150	90	35	35	24	2000
61830.W0006	188	180	41	41	80	3500
61830.W0005	155	150	30	25	64	2500
61830.W0003	144	122	40	23	48	1000