



61850

ANTI-VIBRATION

Material

Rubber (hardness - Shore 55 A).

Technical Notes

Used in a wide range of vibrating

machines.

Allows high deformation with excellent spring back characteristics.

Supports axial and radial loads but not

designed for traction or tension loads. For radial loads please contact our technical team.

Order No.	d ₁	h ₁	d ₂
61850.W0020	20	15	6
61850.W0030	30	20	8
61850.W0031	30	22	8
61850.W0035	35	30	12
61850.W0036	35	40	12
61850.W0040	40	30	10
61850.W0045	45	35	10
61850.W0046	45	45	10
61850.W0050	50	45	10
61850.W0060	60	40	12
61850.W0070	70	45	14
61850.W0080	80	50	16
61850.W0081	80	80	20
61850.W0093	93	120	20
61850.W0100	100	60	20
61850.W0102	100	147	20
61850.W0110	110	70	22
61850.W0130	130	60	25
61850.W0148	148	190	50
61850.W0160	160	100	30
61850.W0170	170	110	31
61850.W0200	200	125	70
61850.W0250	250	300	60