



## 75130

CRANKED & REVOLVING HANDLES

### Material

Grip: duroplast PF 31, black matt.  
Stud & housing: stainless steel, AISI 303.

### Technical Notes

Temperature range 110°C. For certain minimum quantities custom colours

available upon request.

Order No.	$d_1$	$d_2$	$l_1$	$l_2$	A/F	Weight g
75130.W0017	17	M 6	40	13	3	18
75130.W0020	21	M 6	50	13	3	35
75130.W0023	23	M 8	55	14	4	49
75130.W0025	25	M 8	65	15	4	73
75130.W0027	28	M 8	85	15	4	106
75130.W0028	28	M10	85	17	5	110