




# Cam Latches - Flexi-System

insert driver - fixed grip - zinc



## A1003

CAM LATCHES

### Material

Body & insert: die cast zinc. Finished in chrome plate or black powder coating. Insert fitted with O'ring to achieve IP54 rating. Internal spring provides 1.5mm torsion.

**Supplied with:** Nut: steel, zinc plated. Sealing washer: PU and rubber.

**Not supplied:** CAM nor KEY - order separately.

### Technical Notes

Order cam and key separately.

**Cams:** see suitable cam A0203, A0224 and A0240. Select „without projection“ cam type.

Dimensions ch and cl relate to cam. Use formula to calculate ch (required cam off-set), and refer to cam selection chart;

$ch = h - lh$  where;

ch = required cam off-set/height.

h = grip length (distance between inside of latch face and front of cam).

lh = body length of cam latch/lock to be used (see product table below).

**Keys:** see A0102.

**Rods & Guides:** to achieve 3-point latching - A0303, A0321, A0325.

### Important Notes

Extended body version - A1251.

Sold subject to pack quantity.

Order No.	Finish	Insert driver	d <sub>1</sub>	h <sub>1</sub>	lh
A1003.HW0010	Chrome Plated	Square 7	28	6	18
A1003.HW0020	Chrome Plated	Square 8	28	6	18
A1003.HW0040	Chrome Plated	Triangle 7	28	6	18
A1003.HW0050	Chrome Plated	Triangle 8	28	6	18
A1003.HW0060	Chrome Plated	3mm Double Bit	28	6	18
A1003.HW0070	Chrome Plated	4mm Double Bit	28	6	18
A1003.HW0080	Chrome Plated	Slotted (2x4)	28	6	18
A1003.HW0310	Black Coated	Square 7	28	6	18
A1003.HW0320	Black Coated	Square 8	28	6	18
A1003.HW0340	Black Coated	Triangle 7	28	6	18
A1003.HW0360	Black Coated	3mm Double Bit	28	6	18
A1003.HW0370	Black Coated	4mm Double Bit	28	6	18
A1003.HW0380	Black Coated	Slotted (2x4)	28	6	18