


## **Cam Latches - with Rod Control**

extended cover - fixed grip - 2 off 25 x 50 cut out







A4260

## Material

Body: polyamide. Unique integral polyurethane gasket, to achieve IP54 rating. Rod control mechanism: die cast zinc. Driver Insert: die cast zinc, chrome plated. **Not supplied:** Key: order separately.

## **Technical Notes**

Order cam and key separately.

**Cams:** see suitable cam A0203, A0224 and A0240. Select "without projection" cam type.

Dimensions ch and cl relate to cam. Use formula to calculate ch (required cam offset), and refer to cam selection chart; **ch = h - lh** where;

**ch** = required cam off-set/height.

**h** = grip length (distance between inside of latch face and front of cam).

lh = body length of cam latch/lock to be
used (see product table below).

Keys: see A0102.

**Rods & Guides:** to achieve 3-point latching - A0303, A0321, A0325.

| Order No.    |
|--------------|
| A4260.AW0010 |

Insert driver
3mm Double Bit

157.4

w 32.4 lh 22

