


Swing Handles - Cam Control 40mm euro cylinder lock - dust cover - polyamide





B1091

Material

Body & Handle: polyamide, PA6, black.
Cylinder lock: die cast zinc, chrome plated.
Supplied with: Keys: two per lock.
Not supplied: Cam: order separately.
Supplied with: Keys: two per lock.
Not supplied: Cam: order separately.

Technical Notes

Order cam separately.

Cams: see suitable cam A0203, A0224 and

A0240. Select "without projection" cam type.

Dimensions ch and cl relate to cam. Use formula to calculate ch (required cam offset), and refer to cam selection chart; **ch = h - lh** where;

ch = required cam off-set/height.h = grip length (distance between inside of latch face and front of cam).

lh = body length of cam latch/lock to be

used (see product table below).

Rods & Guides: to achieve 3-point latching - A0303, A0321, A0325.

Tips

Also available with radial pin lock, subject to min. order quantity.

Ideal for electrical cabinets, telecom racks or enclosures max. panel thickness of 2mm. For use inside of cabinet gasket. Universal left/right.

Order No.	Finish	Lock type	Key type	I_1	w_1	lh
B1091.AW0020	Black, Plastic	40 Euro	Keyed Alike	160	35	16

