


# **Swing Handles - Cam Control**

40mm euro cylinder lock - dust proof cover - plastic





**B1092** 

#### Material

Body & Handle: polyamide, PA6, black. Cylinder lock: die cast zinc, chrome plated. **Supplied with:** Keys: two per lock. **Not supplied:** Cam: order separately.

### **Technical Notes**

Order cam separately.

**Cams:** see suitable cam A0203, A0224 and A0240. Select "without projection" cam

## type.

Dimensions ch and cl relate to cam. Use formula to calculate ch (required cam offset), and refer to cam selection chart;

ch = h - lh where;

**ch** = required cam off-set/height.

**h** = grip length (distance between inside of latch face and front of cam).

**lh** = body length of cam latch/lock to be

used (see product table below).

**Rods & Guides:** to achieve 3-point latching - A0303, A0321, A0325.

#### Tips

Ideal for electrical cabinets, telecom racks or enclosures max. panel thickness of 2mm. For use inside of cabinet gasket. Universal left/right.

Order No.	Finish	Lock type	Key type	1	w	lh
B1092.AW0010	Black, Plastic	40 Euro	Keyed Alike	165	35	16



