


## Swing Handles - with Rod Control 40mm euro cylinder lock - sliding cover - polyamide





**B2450** 

## Material

Body: polyamide plastic, black. Handle: die cast zinc. chrome plated. Cylinder lock: die cast zinc, chrome plated. Rod Control Mechanism: die cast zinc. **Supplied with:** Keys: two per lock.

## **Technical Notes**

Achieves 2 point clamping at top and

bottom of panel. Not suitable for 3 point clamping.

Unlock handle to release, lift and turn to activate rod control mechanism and release panel.

Sliding lock cover prevents ingress of dust etc. into lock mechanism.

## Tips

Suitable for panel thickness 1 to 2mm.

Order No.	Finish	Lock type	Key type	1	W	lh	а	b	dm stroke 135°	dm stroke 90°
B2450.AW0010	Black Coated	40 Euro	Keyed Alike	347	36	20	113.8	233.2		16.0

