



## E2070

CATCHES & LATCHES

### Material

Strike and catch: polyacetal.  
Roller: polyethylene.

### Technical Notes

This catch has been tested to 300,000 cycles.

Screws not supplied.

| Order No.    | Finish | a    | Push in force<br>kg | Pull out force<br>kg | b  | c <sub>1</sub> | c <sub>2</sub> | c <sub>3</sub> | c <sub>4</sub> | Weight<br>g |
|--------------|--------|------|---------------------|----------------------|----|----------------|----------------|----------------|----------------|-------------|
| E2070.AC0010 | White  | 29.0 | 1.1                 | 1.6                  | 12 | 21.2           | 21.5           | 6.0            | 20.0           | 3           |
| E2070.AC0015 | Brown  | 31.3 | 2.2                 | 3.2                  | 14 | 27.2           | 24.4           | 7.5            | 23.6           | 4           |

  

| Order No.    | d    | d <sub>1</sub> | d <sub>2</sub> | e | f   | g  | h    | i   | j   |
|--------------|------|----------------|----------------|---|-----|----|------|-----|-----|
| E2070.AC0010 | 11.3 | 3,1x7          | 3.0            | 8 | 2.0 | 26 | 13.5 | 7.5 | 1.7 |
| E2070.AC0015 | 12.6 | 3,1x7          | 3.1            | 9 | 2.3 | 32 | 16.5 | 9.0 | 2.0 |

