



**E5850**

**Material**

Body: polypropylene.  
Yoke: steel.  
Strike: steel, nickel or chrome plated.

b, to suit your application.  
Moveable magnet enables better positioning to ensure full surface contact with strike, and hence full magnetic force.

pressure to plastic housing only, to avoid damage to the magnet.

**Technical Notes**

Catches can be used with either strike a or

**Tips**

When installing magnet, use tube to apply

Order No.	Type	Magnetic force kgf	Finish	t	d	d <sub>1</sub>	d <sub>2</sub>	l	Weight g
E5850.AC0010	Magnet	2.5	White	-	-	-	-	-	6.0
E5850.AC0020	Magnet	2.5	Black	-	-	-	-	-	6.0
E5850.AC0703	Strike A	-	Chrome Plated	2.5	12	6	3	-	1.7
E5850.AC0704	Strike A	-	Nickel Plated	3.0	15	8	4	-	3.3
E5850.AC0713	Strike B	-	Nickel Plated	2.5	12	-	-	12	2.0

