



## J0400

DRAW LATCHES

### Material

Steel, Fe P02 + P12, UNI5866, zinc plated.  
Or stainless steel AISI 304, UNI x5crNi.

### Technical Notes

Supplied with counter strike.

Order No.	Finish	$l_1$	$w_1$ $\pm 0.5$	$h$ $\pm 0.5$	$\varnothing d_1$	$\varnothing d_2$	$l_2$	$l_3$	$l_4$ $\pm 0.5$	Weight g
J0400.AC0004	Zinc Plated Steel	193.5	43	19	5.3	4	112	21.5	90	190
J0400.AC0030	Stainless Steel	193.5	43	19	5.3	4	112	21.5	90	190

  

Order No.	$l_5$	$l_6$	$l_7$ $\pm 0.5$	$l_8$	$l_9$	$w_2$ $\pm 0.5$	$w_3$	Load N max.	Tension N max.
J0400.AC0004	66	31.5	58.5	25.5	15	30	27	2000	4000
J0400.AC0030	66	31.5	58.5	25.5	15	30	27	2000	4000