





Draw Latches



J0428

DRAW LATCHES

Material

Steel, Fe P02 + P12, UNI5866, zinc plated.
Or stainless steel AISI 304, UNI x5crNi.

Technical Notes

Supplied with counter strike.

Order No.	Finish	l ₁	w ₁	h	Ø d ₁	Ø d ₂	l ₂	l ₁₀	l ₃	l ₄	Weight g
J0428.AC0004	Zinc Plated Steel	140.5	34	12.5	4.1	3	86	11.5	16	70	75
J0428.AC0030	Stainless Steel	140.5	34	12.5	4.1	3	86	11.5	16	70	75
Order No.	l ₅	l ₆	l ₇ ±0.5	l ₈	l ₉	w ₂	w ₃		Load N max.	Tension N max.	
J0428.AC0004	43	22.5	38	20	8	23	19		1500	3000	
J0428.AC0030	43	22.5	38	20	8	23	19		1500	3000	