




J0480

DRAW LATCHES

Material

Steel, Fe P02 + P12, UNI5866, zinc plated.
Or stainless steel AISI 304, UNI x5crNi.

Technical Notes

Supplied with counter strike.

Order No.	Finish	l_1	h_1	w_1	$\varnothing d_1$	$\varnothing d_2$	l_2	h_2 ± 0.5	Weight g
J0480.AC0004	Zinc Plated Steel	52	11	33	3.5	2	34	12	20
J0480.AC0030	Stainless Steel	52	11	33	3.5	2	34	12	20

Order No.	l_3	l_4	l_5	l_6 ± 0.5	w_2	w_3 -1 0	w_4	Load N max.	Tension N max.
J0480.AC0004	16	18	13	28.5	28	23	15	550	1500
J0480.AC0030	16	18	13	28.5	28	23	15	550	1500