


Concealed Pivot Hinges - Lift Off

20-24mm door return - weld and oval head screw

Hinges

HINGES



Material

Hinge & pin: steel, white zinc plated.

Technical Notes

Suited to sheet metal and machine enclosures with door return of 20-24mm. Main body mounted via two M6 screws, hinge plate welded to frame.

Removable hinge pin enables easy installation, and is held in place via circlip. Max. opening angle 120°.


Important Notes

dr= Maximum door return suitable for use

with hinge.

mc= Minimum clearance advised between
enclosure cover and body to ensure
smooth, full opening of enclosure cover.

Order No.	Door return	Size	F _x N	F _y N	mc min.	ts panel thickness
S2121.AW0020	20.0	60,0 x 32,5 x 20,0	350	778	3	2.0
S2121.AW0024	24.5	60,0 x 38,5 x 24,5	350	778	3	2.0






Hinges


HINGES



A variety of mounting methods are available!



Important Note: Refer to individual product pages for suitable mounting options. If you have any problems please contact our Technical Sales Team.



wixroyd.com

Mounting example

In the example, mounting option (2), a nut with a countersunk screw, is used to mount the hinge onto the enclosure body.



ov-WS1901-A-THH0400-WS2300-A-THH1200-mounting-of-concealed-hinges-lnh - Updated - 01-11-2022

2