





65520

Material

Steel, silver zinc plated, ball stud:
minimum tensile strength $R_m=600\text{N/mm}^2$.
Housing: minimum tensile strength
 $R_m=500\text{N/mm}^2$.

Technical Notes

Similar to DIN 71802, *M14x1,5 is a fine pitch thread.


Tips

Standard thread is right hand, (for left hand thread see 65522).
For stainless steel version see 65524.

Order No.	Thread hand	d_1 tol. h9	d_2	l_1	d_3 ± 0.5	d_4 ± 0.5	l_2	l_3	l_4	Extraction force N	Weight g
65520.W0005	Right	8	M 5	22	8	12.8	19.2	9	10.2	30	15.2
65520.W0006	Right	10	M 6	25	10	14.8	23.5	11	11.5	40	25.2
65520.W0008	Right	13	M 8	30	13	19.3	29.5	13	14.0	60	53.1
65520.W0010	Right	16	M10	35	16	24.0	36.0	16	15.5	80	103.8
65520.W0014	Right	19	M14x1,5*	45	22	30.0	48.0	20	21.5	100	220.9



65522



Material

Steel, silver zinc plated, ball stud:
minimum tensile strength $R_m=600N/mm^2$.
Housing: minimum tensile strength

$R_m=500N/mm^2$.

Technical Notes



Similar to DIN 71802, *M14x1,5 is a fine

pitch thread.

Tips

For stainless steel version see 65526.

Order No.	Thread hand	d_1 tol. h9	d_2	l_1	d_3 ± 0.5	d_4 ± 0.5	l_2	l_3	l_4	Extraction force N	Weight g
65522.W0005	Left	8	M5	22	8	12.8	19.2	9	10.2	30	15.2
65522.W0006	Left	10	M6	25	10	14.8	23.5	11	11.5	40	25.2
65522.W0008	Left	13	M8	30	13	19.3	29.5	13	14.0	60	53.1
65522.W0010	Left	16	M10	35	16	24.0	36.0	16	15.5	80	103.8
65522.W0014	Left	19	M14x1,5*	45	22	30.0	48.0	20	21.5	100	220.9



65524

Material

Stainless steel (AISI 303).

pitch thread.

Technical Notes

Similar to DIN 71802, *M14x1,5 is a fine


Tips

Standard thread is right hand, (for left hand thread see 65526).

Order No.	Thread hand	d ₁ tol. h9	d ₂	l ₁	d ₃ ±0.5	d ₄ ±0.5	l ₂	l ₃	l ₄	Extraction force N	Weight g
65524.W0005	Right	8	M5	22	8	12.8	19.2	9	10.2	30	15.2
65524.W0006	Right	10	M6	25	10	14.8	23.5	11	11.5	40	25.2
65524.W0008	Right	13	M8	30	13	19.3	29.5	13	14.0	60	53.1
65524.W0010	Right	16	M10	35	16	24.0	36.0	16	15.5	80	103.8
65524.W0014	Right	19	M14x1,5*	45	22	30.0	48.0	20	21.5	100	220.9



65526



Material

Stainless steel (AISI 303).

Technical Notes

Similar to DIN 71802, *M14x1,5 is a fine pitch thread.

Order No.	Thread hand	d ₁ tol. h9	d ₂	l ₁	d ₃ ±0.5	d ₄ ±0.5	l ₂	l ₃	l ₄	Extraction force N	Weight g
65526.W0005	Left	8	M5	22	8	12.8	19.2	9	10.2	30	15.2
65526.W0006	Left	10	M6	25	10	14.8	23.5	11	11.5	40	25.2
65526.W0008	Left	13	M8	30	13	19.3	29.5	13	14.0	60	53.1
65526.W0010	Left	16	M10	35	16	24.0	36.0	16	15.5	80	103.8
65526.W0014	Left	19	M14x1,5*	45	22	30.0	48.0	20	21.5	100	220.9