


Push-Pull Type Toggle Clamp safety knob

Safety Lever Toggle Clamps





41895

Material

Body: steel, zinc plated.

Rivets: stainless steel running in hardened bushes. Pre-lubricated bearings (grease suitable for food industry use).

Handle: ergonomic soft feel, oil-resistant with a large grip area.

Technical Notes

The safety knob holds the clamp in both the open and the closed position. This prevents opening under vibration or inadvertent movement of the clamping arm when loading or unloading a fixture. Without angle bracket. Push and pull-

clamping (equal operation of rod and lever). Long rod-guide with attaching thread and nut.

Temperature range -10°C to +80°C.

Order No.	Size	F_1	F_2	Clamping screw	d_1	d_2	h_1	h_2	I_1	l ₂	l ₃	l ₄	I ₅	I ₆	W_1	W_2	Weight
		kN	kN								min. max.						g
41895.W0003	3	2,5	2,5	M 8x35	M20x1,5	12	86	103	140	134	22-35	56	30	22	36	27	402

