

**Wixroyd**

**9400**



**Material**

Special steel, brown finish tempered.

**Technical Notes**

X is preferred size.  
\* Pin size is equal to stated size  
-0.1mm, tolerance h12.



**Adjustable Pin Face Spanners**  
with welded pins



| Order No. | Size     |       |      |     |   |     |     |
|-----------|----------|-------|------|-----|---|-----|-----|
| 9400.W041 | 7 - 40   | 1,5   | 2,0  | 115 | 3 | 40  | 40  |
| 9400.W042 | 7 - 40   | 2,0 x | 2,5  | 115 | 3 | 40  | 40  |
| 9400.W043 | 7 - 40   | 2,5   | 3,0  | 115 | 3 | 40  | 40  |
| 9400.W061 | 11 - 60  | 3,0   | 4,0  | 160 | 4 | 140 | 140 |
| 9400.W062 | 11 - 60  | 4,0 x | 5,0  | 160 | 4 | 140 | 140 |
| 9400.W063 | 11 - 60  | 5,0   | 6,0  | 160 | 4 | 140 | 140 |
| 9400.W101 | 14 - 100 | 5,0   | 6,0  | 215 | 6 | 300 | 300 |
| 9400.W102 | 14 - 100 | 6,0 x | 7,0  | 215 | 6 | 300 | 300 |
| 9400.W103 | 14 - 100 | 8,0   | 8,0  | 215 | 6 | 300 | 300 |
| 9400.W125 | 22 - 125 | 8,0 x | 8,0  | 260 | 6 | 500 | 500 |
| 9400.W126 | 22 - 125 | 10,0  | 10,0 | 260 | 6 | 500 | 500 |
| 9400.W127 | 22 - 125 | 12,0  | 12,0 | 260 | 6 | 500 | 500 |

**Wixroyd**

**9402**

**Material**

Special steel, brown finish tempered.

**Technical Notes**

\* Pin size is equal to stated size  
-0.1mm, tolerance h12.  
For replacement pins see part no.  
9536 page 833.



**Adjustable Pin Face Spanners**  
with replaceable pins



| Order No. | Size     |   |   |     |   |     |     |
|-----------|----------|---|---|-----|---|-----|-----|
| 9402.W061 | 11 - 60  | 3 | 4 | 160 | 4 | 140 | 140 |
| 9402.W062 | 11 - 60  | 4 | 5 | 160 | 4 | 140 | 140 |
| 9402.W063 | 11 - 60  | 5 | 6 | 160 | 4 | 140 | 140 |
| 9402.W101 | 14 - 100 | 5 | 6 | 215 | 6 | 300 | 300 |
| 9402.W102 | 14 - 100 | 6 | 7 | 215 | 6 | 300 | 300 |
| 9402.W103 | 14 - 100 | 8 | 8 | 215 | 6 | 300 | 300 |

HAND TOOLS