


Dished Washers stainless steel 303



Washers

WASHERS



25500

Material

Stainless steel (AISI 303, 1.4305).

Technical Notes


Similar to DIN 6319D.

Use with spherical seat washer no. 25200 (type C).

Torque values are approximate. Please consider the actual preloads in your appli-

cation and also the coefficient of friction at $\mu 0,12$.


Order No.	For metric thread d_1	For thread d_1 inch	d_2 tol. H13	d_3	h_1	d_4	Load capacity for static load kN max.	Torque Nm max.	With 25200 h_2	Weight g
25500.W0406	M 6	1/4"	7,1	12	2,8	11,0	6	6	4,0	1
25500.W0408	M 8	5/16"	9,6	17	3,5	14,5	12	16	5,3	4
25500.W0410	M10	3/8"	12,0	21	4,2	18,5	16	32	6,3	7
25500.W0412	M12	1/2"	14,2	24	5,0	20,0	24	56	7,9	11
25500.W0416	M16	5/8"	19,0	30	6,2	26,0	45	135	9,3	19
25500.W0420	M20	3/4"	23,2	36	7,5	31,0	71	280	11,6	32
25500.W0424	M24	7/8"	28,0	44	9,5	37,0	105	455	14,9	63
25500.W0430	M30	1-1/8", 1-3/16"	35,0	56	12,0	49,0	191	1050	18,8	127
25500.W0436	M36	1-1/4", 1-3/8"	42,0	68	15,0	60,0			23,4	234
25500.W0442	M42	1-1/2"	49,0	78	18,0	70,0			28,3	362
25500.W0448	M48	1-3/4"	56,0	92	22,0	82,0			35,0	642






Nuts


Available in heat treated steel, unless stated otherwise.




24000 T-Nut, Strength Class 10 DIN 508.



24010 T-Nut with Anti-Slip Device.



24100 Extended T-Nut, Strength Class 10.



24120 Rhombus T-Nuts



24300 Fixture Nuts, Strength Class 10 - DIN 6330B



24400 Collar Nuts, DIN 6331



24502 Fast Nut - With Collar Rapid Assembly Nut



24520 - Steel Slip-On Lock Nuts - Rapid Assembly Nut.



24600 Extension Nuts, Strength Class 10.



24620 Swivel Nuts, Conical Seat

Washers

Available in a range of steel types - see product for details.



25000 - Hardened Steel - Plain Washers, DIN 6340.



25100 - Case Hardened Steel - Spherical Seat Washers, Type C - DIN 6319C.



25400 - Case Hardened Steel - Dished Washers, Type D - DIN 6319D.



25700 - Tempered Steel - Dished Washers, Type G - DIN 6319G.



25900 - Stainless Steel Compact Spherical Washer, Conical Seat, similar to DIN6319