




Plastic Pull Handles through hole or threaded bush



79150

PULL HANDLES

Material

Thermoplastic, black, matt, glass fibre reinforced.

Threaded bush: brass.

Technical Notes

Other colours on request: red, orange,

white & grey - subject to minimum quantity.

| Order No. | Type | l_1 | l_2 | b_1 | d_2 | h_1 | h_2 | t_1 | t_2 | $\varnothing d_1$ | Weight g |
|-------------|-------------|-------|-------|-------|-------|-------|-------|-------|-------|-------------------|----------|
| 79150.W0010 | Front Mount | 93.5 | 112 | 21 | Ø10,5 | 36 | 30 | 6 | 7 | 6.5 | 26 |
| 79150.W0011 | Front Mount | 117.0 | 139 | 26 | Ø10,5 | 41 | 34 | 6 | 9 | 6.5 | 41 |
| 79150.W0012 | Front Mount | 117.0 | 139 | 26 | Ø13,0 | 41 | 34 | 6 | 9 | 8.5 | 40 |
| 79150.W0013 | Front Mount | 132.0 | 156 | 27 | Ø10,5 | 45 | 37 | 9 | 7 | 6.5 | 56 |
| 79150.W0014 | Front Mount | 132.0 | 156 | 27 | Ø13,0 | 45 | 37 | 7 | 9 | 8.5 | 54 |
| 79150.W0018 | Front Mount | 179.0 | 204 | 28 | Ø13,0 | 50 | 42 | 8 | 9 | 8.5 | 72 |
| 79150.W0509 | Rear Mount | 93.5 | 112 | 21 | - | 36 | 30 | - | 9 | M 5 | 33 |
| 79150.W0510 | Rear Mount | 93.5 | 112 | 21 | - | 36 | 30 | - | 9 | M 6 | 33 |
| 79150.W0511 | Rear Mount | 117.0 | 139 | 26 | - | 41 | 34 | - | 9 | M 6 | 47 |
| 79150.W0512 | Rear Mount | 117.0 | 139 | 26 | - | 41 | 34 | - | 9 | M 8 | 49 |
| 79150.W0513 | Rear Mount | 132.0 | 156 | 27 | - | 45 | 37 | - | 9 | M 6 | 62 |
| 79150.W0514 | Rear Mount | 132.0 | 156 | 27 | - | 45 | 37 | - | 9 | M 8 | 64 |
| 79150.W0518 | Rear Mount | 179.0 | 204 | 28 | - | 50 | 42 | - | 9 | M 8 | 82 |