


Cam Latch - Flush T-handle

vertical - heavy duty - fixed grip - standard cylinder

Paddle Latches



B4586

PADDLE LATCHES

Material

Body: stainless steel, AISI 303.

Handle: die cast zinc, chrome plated.

Cylinder lock: die cast zinc, chrome plated.

Supplied with: Keys: two per lock.

Cam: stainless steel, AISI 303.

Technical Notes

Hole fixing type requires 4 off M 6 screws

(not supplied), for front mounting.

Stud fixing type has 4 off M 6 welded studs for near mounting with M 6 nuts (not supplied).

Tips

Ideal for electricity sub-stations, HGVs and other road side vehicles.


T-handle is in the vertical position when


locked. Universal left/right. For use inside of cabinet gasket.


Can be used with cam range A0203.

Order No.	Mounting type	Lock type	Key type	lh
B4586.AW0010	Hole Fixing	Std. Cylinder	Keyed Alike	25
B4586.AW0020	Stud Fixing	Std. Cylinder	Keyed Alike	25



	Cylinder Profile	Body	Locking System		Use	Cam Type
	Std. Cylinder Lock 40mm Euro Padlockable Insert Driver	Die-Cast Zinc Polyamide Plastic Stainless Steel Steel Aluminium	IP Rating	1-point 2-point 3-point	Inside Gasketing Outside Gasketing With Projection W/O Projection	
B1180 - Swing Handle 	✓	✓	54	✓ ✓ ✓	✓	✓
Cams: A0203, A0224, A0240 - Keys: Supplied						

	Cylinder Profile	Body	Locking System		Use	Cam Type
	Std. Cylinder Lock 40mm Euro Padlockable Insert Driver	Die-Cast Zinc Polyamide Plastic Stainless Steel Steel Aluminium	IP Rating	1-point 2-point 3-point	Inside Gasketing Outside Gasketing With Projection W/O Projection	
B4584 - Cam Latch - Flush T-handle, Vertical - Heavy Duty 	✓	✓		✓ ✓	✓	✓
Cams: Supplied - Keys: Supplied						
B4586 - Cam Latch - Flush T-handle, Vertical - Heavy Duty 	✓	✓		✓ ✓	✓	✓
Cams: Supplied - Keys: Supplied						
B4588 - Cam Latch - Flush T-handle, Vertical - Heavy Duty 	✓	✓		✓ ✓	✓	✓
Cams: Supplied - Keys: Supplied						

	Cylinder Profile	Body	Locking System		Use	Cam Type
	Std. Cylinder Lock 40mm Euro Padlockable Insert Driver	Die-Cast Zinc Polyamide Plastic Stainless Steel Steel Aluminium	IP Rating	1-point 2-point 3-point	Inside Gasketing Outside Gasketing With Projection W/O Projection	
B4590 - Cam Latch - Flush T-handle - Heavy Duty 	✓	✓		✓ ✓ ✓	✓	✓
Cams: Supplied - Keys: Supplied						



Cam Latches

flush T-handle

Swing Handles & Paddle Latches

Models available



Cam Latch - Flush T-Handle with rod control for multi-point latching



Cam Latch - Flush T-Handle for single point latching



Cam Latch - Flush T-Handle with adjustable grip



Cam Latch - Concealed T-Handle for electricity panels

Variety of materials

- Steel.
- Stainless steel.
- Aluminium.
- Polyamide.

Actuation/locking method

- Blank, without lock.
- Standard cylinder Lock.
- Padlockable T-Handle actuation.

Features

- Heating & ventilation.
- Generators.
- Compressors.
- Machine covers.

- Electric panels.
- Off-road equipment.
- Industrial transport.
- Special equipment cases.

Applications