





Slottex Plugs threaded

Caps, Plugs, Masking and



V0400



Material

Polyamide, yellow.

spanner.

Technical Notes

Threaded for installation via screwdriver or


Important Notes

Sold subject to minimum pack quantity.

Order No.	d ₁	l ₁	l ₂	A/F	d ₂
V0400.AC0881	14,2 - 0,2	7	10	10	M10
V0400.AC0883	17,2 - 0,2	10	10	13	M12
V0400.AC0885	19,2 - 0,2	10	10	13	M14
V0400.AC0887	22,0 - 0,2	10	10	17	M16
V0400.AC0889	24,0 - 0,2	10	11	17	M18
V0400.AC0891	26,0 - 0,2	10	14	19	M20
V0400.AC0893	27,2 - 0,2	10	14	19	M22
V0400.AC0895	32,0 - 0,3	13	14	24	M26
V0400.AC0897	32,3 - 0,3	13	14	24	M27
V0400.AC0899	40,0 - 0,4	13	14	27	M33
V0400.AC0901	50,0 - 0,4	13	15	36	M42
V0400.AC0949	16,8	9	10	13	1/8"
V0400.AC0951	19,0 - 0,2	9	10	13	1/4"
V0400.AC0953	22,2 - 0,2	9	11	17	3/8"
V0400.AC0955	27,0 - 0,2	12	13	19	1/2"
V0400.AC0957	32,3 - 0,3	12	13	24	3/4"
V0400.AC0959	40,0 - 0,4	15	14	27	1"
V0400.AC0961	50,0 - 0,4	15	15	36	1 1/4"
V0400.AC0963	55,4 - 0,4	15	15	41	1 1/2"
V0400.AC0965	68,4	15	15	55	2"




V0440



Material
Low density polyethylene, red.


Important Notes
Sold subject to minimum pack quantity.

Order No.	d ₁	l ₁	t	d ₂
V0440.AC0851	1/4"	7.0	3.5	19.0
V0440.AC0853	3/8"	8.5	3.5	22.5
V0440.AC0855	1/2"	10.0	4.5	26.0
V0440.AC0857	3/4"	11.5	6.0	32.0
V0440.AC0859	1"	13.5	6.0	37.0



Sealing Slotex Plugs threaded

Caps, Plugs,
Masking and



V0420

CAPS, PLUGS, MASKING AND INSERTS

Material

Low density polyethylene, yellow.

Important Notes

Sold subject to minimum pack quantity.

Order No.	d_1	l	t	d_2
V0420.AC0781	21	9	5	1/8"
V0420.AC0783	21	9	5	1/4"
V0420.AC0785	23	10	6	3/8"
V0420.AC0787	28	12	6	1/2"
V0420.AC0801	21	9	5	M12
V0420.AC0803	21	9	5	M14
V0420.AC0805	23	10	6	M16
V0420.AC0807	23	10	6	M18
V0420.AC0809	28	12	6	M20
V0420.AC0811	28	12	6	M22