




# Cam Latch - Flush T-handle - Rod

vertical - heavy duty- fixed grip - standard cylinder

## Paddle Latches



### B4584

PADDLE LATCHES

#### Material

Body: stainless steel, AISI 303.

Handle: die cast zinc, chrome plated.

Cylinder lock: die cast zinc, chrome plated.

**Supplied with:** Keys: two per lock.

#### Technical Notes

Hole fixing type requires 4 off M 6 screws

(not supplied) for front mounting.

Stud fixing type has 4 off M 6 welding studs for rear mounting with M 6 nuts (not supplied).

Use with multi-point latching rods (e.g A0303), with 8mm Ø rods, to achieve two point latching of larger enclosure panels.

#### Tips


Ideal for electricity sub-stations, HGVs and other road side vehicles.

T-handle is in the vertical position when locked. Universal left/right. For use inside of cabinet gasket.

| Order No.    | Mounting type | Lock type     | Key type    |
|--------------|---------------|---------------|-------------|
| B4584.AW0010 | Hole Fixing   | Std. Cylinder | Keyed Alike |
| B4584.AW0020 | Stud Fixing   | Std. Cylinder | Keyed Alike |



B4586



**Material**

Body: stainless steel, AISI 303.  
Handle: die cast zinc, chrome plated.  
Cylinder lock: die cast zinc, chrome plated.  
**Supplied with:** Keys: two per lock.  
Cam: stainless steel, AISI 303.

**Technical Notes**

Hole fixing type requires 4 off M 6 screws


(not supplied), for front mounting.  
Stud fixing type has 4 off M 6 welded studs for near mounting with M 6 nuts (not supplied).

**Tips**

Ideal for electricity sub-stations, HGVs and other road side vehicles.  
T-handle is in the vertical position when

locked. Universal left/right. For use inside of cabinet gasket.  
Can be used with cam range A0203.


| Order No.    | Mounting type | Lock type     | Key type    | lh |
|--------------|---------------|---------------|-------------|----|
| B4586.AW0010 | Hole Fixing   | Std. Cylinder | Keyed Alike | 25 |
| B4586.AW0020 | Stud Fixing   | Std. Cylinder | Keyed Alike | 25 |



## Cam Latch - Flush T-handle

vertical - heavy duty - adjustable grip - standard

## Paddle Latches



### B4588

PADDLE LATCHES

#### Material

Body: stainless steel, AISI 303.

Handle: die cast zinc, chrome plated.

Cylinder lock: die cast zinc, chrome plated.

**Supplied with:** Keys: two per lock.

Cam: stainless steel, AISI 303.

#### Technical Notes

Hole fixing type requires 4 off M 6 screws

(not supplied), for front mounting.

Stud fixing type has 4 off M 6 welded studs for near mounting with M 6 nuts (not supplied).

#### Tips

Ideal for electricity sub-stations, HGVs and other road side vehicles.

T-handle is in the vertical position when


locked.

For use inside of cabinet gasket.

| Order No.    | Mounting type | Lock type     | Key type    | h grip range |
|--------------|---------------|---------------|-------------|--------------|
| B4588.AW0010 | Hole Fixing   | Std. Cylinder | Keyed Alike | 48 - 58      |
| B4588.AW0020 | Stud Fixing   | Std. Cylinder | Keyed Alike | 48 - 58      |



B4590



**Material**  
Body: stainless steel, AISI 303.  
Handle: die cast zinc, chrome plated.  
Cylinder lock: die cast zinc, chrome plated.

Cam: stainless steel, AISI 303.  
**Technical Notes**  
Mounting via 4 off M 6 screws (not

supplied) for front mounting.  
With lock version has standard cylinder lock to prevent unauthorised opening.


| Order No.    | Mounting type | Lock type       | $I_1$ | $W_1$ | h grip range |
|--------------|---------------|-----------------|-------|-------|--------------|
| B4590.AW0010 | Hole fixing   | Std. Cylinder   | 105   | 120   | 50~60        |
| B4590.AW0020 | Hole fixing   | Blank - No Lock | 105   | 120   | 50~60        |





# Wixroyd Swing Handles

## product selection charts

# Swing Handles & Paddle Latches


| <br>cut out                     | Cylinder Profile                                                | Body                                                                        | Locking System | Use                                                                    | Cam Type                          |
|------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------|-----------------------------------------------------------------------------|----------------|------------------------------------------------------------------------|-----------------------------------|
|                                                                                                                  | Std. Cylinder Lock<br>40mm Euro<br>Padlockable<br>Insert Driver | Die-Cast Zinc<br>Polyamide Plastic<br>Stainless Steel<br>Steel<br>Aluminium | IP Rating      | 1-point<br>2-point<br>3-point<br>Inside Gasketing<br>Outside Gasketing | With Projection<br>W/O Projection |
| <br><b>B1180 - Swing Handle</b> | ✓                                                               | ✓                                                                           | 54             | ✓<br>✓<br>✓<br>✓                                                       | ✓                                 |
| Cams: A0203, A0224, A0240 - Keys: Supplied                                                                       |                                                                 |                                                                             |                |                                                                        |                                   |

| <br>cut out                                                | Cylinder Profile                                                | Body                                                                        | Locking System | Use                                                                    | Cam Type                          |
|---------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------|-----------------------------------------------------------------------------|----------------|------------------------------------------------------------------------|-----------------------------------|
|                                                                                                                                             | Std. Cylinder Lock<br>40mm Euro<br>Padlockable<br>Insert Driver | Die-Cast Zinc<br>Polyamide Plastic<br>Stainless Steel<br>Steel<br>Aluminium | IP Rating      | 1-point<br>2-point<br>3-point<br>Inside Gasketing<br>Outside Gasketing | With Projection<br>W/O Projection |
| <br><b>B4590 - Cam Latch - Flush T-handle - Heavy Duty</b> | ✓                                                               | ✓                                                                           | ✓              | ✓<br>✓                                                                 | ✓                                 |
| Cams: Supplied - Keys: Supplied                                                                                                             |                                                                 |                                                                             |                |                                                                        |                                   |

| <br>cut out                                                            | Cylinder Profile                                                | Body                                                                        | Locking System | Use                                                                    | Cam Type                          |
|---------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------|-----------------------------------------------------------------------------|----------------|------------------------------------------------------------------------|-----------------------------------|
|                                                                                                                                                         | Std. Cylinder Lock<br>40mm Euro<br>Padlockable<br>Insert Driver | Die-Cast Zinc<br>Polyamide Plastic<br>Stainless Steel<br>Steel<br>Aluminium | IP Rating      | 1-point<br>2-point<br>3-point<br>Inside Gasketing<br>Outside Gasketing | With Projection<br>W/O Projection |
| <br><b>B4584 - Cam Latch - Flush T-handle, Vertical - Heavy Duty</b> | ✓                                                               | ✓                                                                           |                | ✓<br>✓                                                                 | ✓                                 |
| Cams: Supplied - Keys: Supplied                                                                                                                         |                                                                 |                                                                             |                |                                                                        |                                   |
| <br><b>B4586 - Cam Latch - Flush T-handle, Vertical - Heavy Duty</b> | ✓                                                               | ✓                                                                           | ✓              | ✓                                                                      | ✓                                 |
| Cams: Supplied - Keys: Supplied                                                                                                                         |                                                                 |                                                                             |                |                                                                        |                                   |
| <br><b>B4588 - Cam Latch - Flush T-handle, Vertical - Heavy Duty</b> | ✓                                                               | ✓                                                                           | ✓              | ✓                                                                      | ✓                                 |
| Cams: Supplied - Keys: Supplied                                                                                                                         |                                                                 |                                                                             |                |                                                                        |                                   |



B4604



Material

Body and Cover: aluminium, grey powder coated.


Technical Notes

Designed for medium voltage electricity panels.

T-handle is in the vertical position when locked. For added security has padlock shackle to prevent lifting/turning of T-handle to suit max. padlock shackle of 9mm dia (not supplied). Use with multi-point latching rods (A0303)

with 8mm Ø rods, to achieve two point latching of larger enclosure panels. Handle secured to frame via mounting brackets (supplied).

| Order No.    | Body      | $h_1$ | $l_1$ |
|--------------|-----------|-------|-------|
| B4604.AW0010 | Aluminium | 178   | 87    |






# Wixroyd Cam Latches

## product selection charts

# Swing Handles & Paddle Latches

|                                                            | Cylinder Profile                                                                    | Body                                                               | Locking System                             | Use                                                                        | Cam Type |
|------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------|--------------------------------------------|----------------------------------------------------------------------------|----------|
|                                                            | Std. Cylinder Lock<br>40mm Euro<br>Padlockable<br>Insert Driver                     | Die-Cast Zinc<br>Polyamide Plastic<br>Stainless Steel<br>Aluminium | IP Rating<br>1-point<br>2-point<br>3-point | Inside Gasketing<br>Outside Gasketing<br>With Projection<br>W/O Projection |          |
| <b>B1450 - Swing Handles - Cam Control - Sliding Cover</b> |    | ✓                                                                  | ✓                                          | ✓                                                                          | ✓        |
| Cams: A0203, A0224, A0240 - Keys: Supplied                 |                                                                                     |                                                                    |                                            |                                                                            |          |
| <b>B2450 - Swing Handles - Rod Control - Sliding Cover</b> |    | ✓                                                                  | ✓                                          | ✓                                                                          | ✓        |
| Cams: N/A - Keys: Supplied                                 |                                                                                     |                                                                    |                                            |                                                                            |          |
| <b>B4604 - Cam Latch - Concealed T-handle, Vertical</b>    |   | ✓                                                                  | 65                                         | ✓                                                                          |          |
| Cams: Supplied - Keys: Padlockable                         |                                                                                     |                                                                    |                                            |                                                                            |          |
| <b>B4703 - Push-to-Close Paddle Latch - Pull-to-Open</b>   |  | ✓                                                                  | ✓                                          | ✓                                                                          |          |
| Cams: N/A - Keys: Supplied                                 |                                                                                     |                                                                    |                                            |                                                                            |          |
| <b>B4713 - Push-to-Close Paddle Latch - Pull-to-Open</b>   |  | ✓                                                                  | ✓                                          | ✓                                                                          |          |
| Cams: N/A - Keys: Supplied                                 |                                                                                     |                                                                    |                                            |                                                                            |          |
| <b>B4733 - Push-to-Close Paddle Latch - Pull-to-Open</b>   |  | ✓                                                                  | ✓                                          | ✓                                                                          |          |
| Cams: N/A - Keys: Supplied                                 |                                                                                     |                                                                    |                                            |                                                                            |          |
| <b>B4750 - Push-to-Close Paddle Latch - Pull-to-Open</b>   |  | ✓                                                                  | ✓                                          | ✓                                                                          |          |
| Cams: N/A - Keys: Supplied                                 |                                                                                     |                                                                    |                                            |                                                                            |          |
| <b>B4752 - Push-to-Close Paddle Latch - Pull-to-Open</b>   |  | ✓                                                                  | ✓                                          | ✓                                                                          |          |
| Cams: N/A - Keys: Supplied                                 |                                                                                     |                                                                    |                                            |                                                                            |          |

|                                                          | Cylinder Profile                                                                    | Body                                                               | Locking System                             | Use                                                                        | Cam Type |
|----------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------|--------------------------------------------|----------------------------------------------------------------------------|----------|
|                                                          | Std. Cylinder Lock<br>40mm Euro<br>Padlockable<br>Insert Driver                     | Die-Cast Zinc<br>Polyamide Plastic<br>Stainless Steel<br>Aluminium | IP Rating<br>1-point<br>2-point<br>3-point | Inside Gasketing<br>Outside Gasketing<br>With Projection<br>W/O Projection |          |
| <b>B4754 - Push-to-Close Paddle Latch - Pull-to-Open</b> |    | ✓                                                                  | ✓                                          | ✓                                                                          |          |
| Cams: N/A - Keys: Supplied                               |                                                                                     |                                                                    |                                            |                                                                            |          |
| <b>B4756 - Push-to-Close Paddle Latch - Pull-to-Open</b> |    | ✓                                                                  | ✓                                          | ✓                                                                          |          |
| Cams: N/A - Keys: Supplied                               |                                                                                     |                                                                    |                                            |                                                                            |          |
| <b>B4758 - Push-to-Close Paddle Latch - Pull-to-Open</b> |   | ✓                                                                  | ✓                                          | ✓                                                                          |          |
| Cams: N/A - Keys: Supplied                               |                                                                                     |                                                                    |                                            |                                                                            |          |
| <b>B4800 - Twist-to-Close Paddle Latch - Snap-On</b>     |  | ✓                                                                  | ✓                                          | ✓                                                                          |          |
| Cams: N/A - Keys: Supplied                               |                                                                                     |                                                                    |                                            |                                                                            |          |



Models available




Cam Latch - Flush T-Handle  
with rod control for multi-point latching



Cam Latch - Flush T-Handle  
for single point latching



Cam Latch - Flush T-Handle  
with adjustable grip



Cam Latch - Concealed T-Handle  
for electricity panels

Features

Variety of materials

- Steel.
- Stainless steel.
- Aluminium.
- Polyamide.

Actuation/locking method

- Blank, without lock.
- Standard cylinder Lock.
- Padlockable T-Handle actuation.

Applications

- Heating & ventilation.
- Generators.
- Compressors.
- Machine covers.

- Electric panels.
- Off-road equipment.
- Industrial transport.
- Special equipment cases.