


Horizontal Toggle Clamps safety lever - open arm - vertical base

Safety Lever Toggle Clamps





41060.1

Material

Body: steel, zinc plated. Rivets: stainless steel running in hardened bushes. Prelubricated bearings (grease suitable for food industry use).

Ergonomic soft feel oil-resistant handle

with large grip area.

Supplied complete with weldable clamping screw (with rubber pad).

Technical Notes

The safety lever holds the clamp in both

the open and the closed position. This prevents opening under vibration or inadvertent movement of the clamping arm when loading or unloading a fixture.


Temperature range -10°C to +80°C.

Order No.	Size	F ₁ kN	F ₂ kN	Clamp	oing screw	h_1	h ₂	h ₃	h ₄	h ₅ min.	h ₅ max.	I_1	l ₂	Weight g
41060.W0003	3	1.8	2.5	M 8x45		65	86	49.0	15	14.5	26	206	73	390
41060.W0004	4	2.0	3.0	M 8x65		97	126	66.5	20	17.5	46	287	113	800
Order No.	l ₃	I ₄	I ₅	I ₆	l ₇	l ₈	w_1	W_2	w ₃	W_4	w ₅	d_1	d_2	α
41060.W0003	38	14	50	25.7	13.0	7	48	8	6	42	37,5-42,5	6.5	5.1	90°
41060.W0004	63	27	57	41.0	20.5	8	51	10	8	59	52,0-59,0	8.5	8.5	90°






Welding Fixtures






Machining and Jig Assemblies





Cmm's





ov-W40000.1-A-T-W42070-A-T-b-rnh- Updated -27-10-2022




Wixroyd Toggle Clamps

overview







Mounting Base Variations

Horizontal base

Vertical base

Angled base

Push-pull





Horizontal acting



Clamping Variations


Vertical acting


Hook type

Latch type

Explanation of forces


The force transmitted to the workpiece by the toggle clamp's closed arm, without itself being deformed when machine forces are applied. The holding force value is dependent upon the proximity of the measuring load point to the toggle clamp's pivot point (therefore two values, F1 and F2 are provided).






Holding Forces F1 or F2

The force applied to the workpiece when the toggle clamp's arm is closed. These clamping forces can only be stated for pneumatic toggle clamps, clamping forces of manual clamps cannot be easily measured as they are dependent upon the operator.



Clamping Forces F₃ or F₄

For pneumatically controlled toggle clamps only, F5 is the piston force required (at 6 bar to) achieve the stated clamping force.



Piston Forces F₅



Wixroyd Toggle Clamps

overview



Quality Features

SAFETY LEVER TOGGLE CLAMPS



Ergonomic soft grip 2-component handle




Stainless rivets and hardened bushings



Moveable stop for variable opening angle



Operator finger protection



Temperature resistant

Unique Features



Safety catches



Heavy duty versions



Pneumatic versions



Matt black surface for optical measurement

Materials



Steel, zinc plated and passivated



Stainless steel (304)



Steel, matt black vario-spektron coated



Protective cap and handle made of an electrostatic conductive (dissipative) material.