


Fixed Catch stainless steel - for 41821.W0002 - .W0004

Stainless Steel Toggle Clamps



Material

Stainless steel (AISI 304, 1.4301), polished.

Technical Notes

For use with toggle clamp no. 41821. W0302 - .W0304.

Order No.	Size	h_1	h ₂	I_1	I ₂	I ₃	w_1	d_1	Weight
41831.W0312	2	5	12	26	11	5	18	5.2	14
41831.W0313	3	6	16	36	14	7	23	6.5	30
41831.W0314	4	8	22	48	19	9	30	8.5	66





Toggle Clamps

Wixroyd Toggle Clamps



Welding Fixtures






Machining and Jig Assemblies





Cmm's







wixroyd.com



Wixroyd Toggle Clamps

overview

Toggle Clamps

STAINLESS STEEL TOGGLE CLAMPS







Mounting Base Variations

Clamping Variations

Horizontal base

Vertical base

Angled base





Vertical acting

Horizontal acting



Hook type

Latch type


Push-pull

Explanation of forces

The force transmitted to the workpiece by the toggle clamp's closed arm, without itself being deformed when machine forces are applied. The holding force value is dependent upon the proximity of the measuring load point to the toggle clamp's pivot point (therefore two values, F1 and F2 are provided).


The force applied to the workpiece when the toggle clamp's arm is closed. These clamping forces can only be stated for pneumatic toggle clamps, clamping forces of manual clamps cannot be easily measured as they are dependent upon the operator.

For pneumatically controlled toggle clamps only, F5 is the piston force required (at 6 bar to) achieve the stated clamping force.



Holding Forces F1 or F2

Clamping Forces F3 or F4



Piston Forces F5



0333 207 4497

sales@wixroyd.com

Toggle Clamps

Wixroyd Toggle Clamps

overview



Quality Features





Ergonomic soft grip 2-component handle




Stainless rivets and hardened bushings



Moveable stop for variable opening angle



Operator finger protection



Temperature resistant


Unique Features



Safety catches



Heavy duty versions



Pneumatic versions



Matt black surface for optical measurement

Materials



Steel, zinc plated and passivated



Stainless steel (304)



Steel, matt black vario-spektron coated



Protective cap and handle made of an electrostatic conductive (dissipative) material.

