


Gripping Pads - Diamond Coated stainless - round - rear fixing

35630



Material

Stainless steel (AISI 630, precipitation-hardened), heat treated to HRc 43-46.

Technical Notes

Permanently fused diamond powder

creates an abrasive surface comparable to 100 grit abrasive value. Ideal for holding smooth or slippery components with a minimum of clamping pressure, and minimal surface marking. Excellent wear resistance.

Order No.	d ₁ +0.00 -0.13	d_2	h ₁ +0.00 -0.13	h ₂
35630.W0841	8	M 4x0,7	10	5.0
35630.W0842	8	M 4x0,7	12	6.4
35630.W1051	10	M 5x0,8	10	5.0
35630.W1052	10	M 5x0,8	12	6.4
35630.W1251	12	M 5x0,8	10	5.0
35630.W1252	12	M 5x0,8	12	6.4
35630.W1661	16	M 6x1,0	10	5.0
35630.W1662	16	M 6x1,0	12	6.4
35630.W2061	20	M 6x1,0	10	5.0
35630.W2062	20	M 6x1,0	12	6.4
35630.W2561	25	M 6x1,0	10	5.0
35630.W2562	25	M 6x1,0	12	6.4



Carbide & Hardened Steel Grippers & Inserts





Grippers enhance workholding for multiple machining operations.



Grippers increase handling capability.

Pads and Gripper Options

Pads



Solid Carbide
High impact carbide
pads, can be brazed or
bonded into place.



Carbide Tipped
Constructed with high impact carbide pad brazed to a heat treated alloy steel body. Mount via tapped hole or a flat on the outside diameter for set screw mounting.



Hardened Steel
Made from 8620 steel,
carburized and hardened
to Rc 58/60 1.2mm with
black oxide finish. Mount
via tapped or counter
bored hole.



Thermoplast
Made from white
thermoplast. Mount
via tapped or counter
bored hole.

Non-marking



Pad from 17-4 stainless steel, hardened to Rc 43/46. Mount via tapped or counter bored hole.

Stainless Steel



Abrasive Diamond Surface
Abrasive surface
permanently fused to a
17-4 stainless steel pad,
hardened to Rc 43/46.
The surface texture is
comparable to a 100 grit
abrasive. Mount via tapped
or counter bored hole.



Soft Urethane Surface
Urethane surface is
permanently bonded to a
300 series stainless steel
pad. The urethane provides
excellent protection
against damage on delicate
work surfaces. Tapped hole
mounting.


see our website for our full range: wixroyd.com

Grippers




High Speed Tool Steel
Manufactured from M-2
high speed tool steel,
hardened to Be 60/62

high speed tool steel, hardened to Rc 60/62 with black oxide finish. Mount via tapped hole, counter bored hole or a flat on the outside diameter for set screw mounting.



Carbide Tipped

Constructed with high impact carbide pad brazed to a heat treated alloy steel body. Mounts via tapped hole or a flat on the outside diameter for set screw mounting.



Solid Carbide

Manufactured from high impact carbide in a solid gripper pad or as a solid gripper body with a threaded brazed-in steel insert. Mount via tapped hole or a flat on the outside diameter for set screw mounting.



Specialist Gripping Pads



Urethane Coated

Abrasive

Diamond Coated

A Range of Specialist Gripping Pads to Suit Your Application



Unique urethane coat prevents marking of delicate components during machining or manipulation by robots. The urethane pad is permanently bonded to the stainless steel body of the gripping pad. With a bubbled texture, air is able to escape and hence avoid any suction action - enabling easy releasing of parts.

These are available in three different urethane durometers.




35 durometer: Pencil rubber top



60 durometer: Car tyre

80 durometer:

Skateboard wheel



To improve handling of smooth or slippery components, with a minimum of clamping pressure, our abrasive diamond coated pads provide an excellent solution.

Diamond powders are permanently fused to a 17-4 stainless pad, to provide an abrasive surface comparable to 100 grit value.



Sandpaper of 100 grit texture

Pads of 17-4 Stainless, hardened to RC 43/46 provide Stainless Pads solutions to applications where material selection is of greater importance; for example nuclear or food



