

### **Double Universal Joint**

Steel

# **Universal Joints**



d<sub>1</sub>

Material Steel (9 SMnPb28k, no. 10718). Bearing type: Plain bearing.

#### **Technical Notes**

To DIN 808/7551, keyways aligned.

Maximum bending angle 45° per joint. Max. drive speed of 1000 rpm.

round

bore

with

keyway

#### Tips

d<sub>2</sub>

¢

Ι<sub>3</sub> Ι<sub>1</sub> 12

Œ

 $I_2$ 

Double universal joints are used where large bending angles are required or where

two shafts offset in relation to each other. Product variations available on request, for square bores change the suffix to SQ for square bores or HX for hex bores. For stainless steel see 65166.

65160

Order No.	Bore dia.	d <sub>1</sub> tol. H7	d <sub>2</sub>	$I_1$	I <sub>2</sub>	I <sub>3</sub>	$I_4$	w <sub>1</sub> tol. JS9	w <sub>2</sub>	Weight g
65160.W0010	Round Bore	10	16	74	26	22	15	-	-	80
65160.W0012	Round Bore	12	22	88	31	26	18	-	-	200
65160.W0016	Round Bore	16	25	104	37	30	21	-	-	300
65160.W0020	Round Bore	20	32	124	43	38	24	-	-	500
65160.W0025	Round Bore	25	42	156	54	48	31	-	-	1200
65160.W0030	Round Bore	30	50	188	66	56	38	-	-	1700
65160.W0040	Round Bore	40	70	238	83	72	47	-	-	4300
65160.W0210	With Keyway	10	16	74	26	22	15	3	11.4	80
65160.W0212	With Keyway	12	22	88	31	26	18	4	13.8	200
65160.W0216	With Keyway	16	25	104	37	30	21	5	18.3	300
65160.W0220	With Keyway	20	32	124	43	38	24	6	22.8	500
65160.W0225	With Keyway	25	42	156	54	48	31	8	28.3	1200
65160.W0230	With Keyway	30	50	188	66	56	38	8	33.3	1700
65160.W0240	With Keyway	40	70	238	83	72	47	12	43.3	4300



0333 207 4497

### Materials Handling

## **Universal Joints**

overview



### **Parts overview**

#### **Single Universal Joints**

Available with plain bearings or needle roller bearings. Plain bore and keyed bores stocked as standard, hex or square shaped bores on request. Bore diameters 6mm up to 50mm.





or needle roller bearings. Plain bore and keyed bores stocked as standard, hex or square shaped bores on request. Bore diameters 6mm up to 50mm.



Single and double universal joints with plain bearings and plain bores. Keyed, hex or square shaped bores available on request. Bore diameters 6mm up to 30mm.



#### **Quick Release Universal Joints**

Quick change mechanism one end of the joint to allow rapid connection and release of the shaft, ideal when time is critical. Bore diameters 8mm up to 30mm.



#### **Universal Joint Bellows**

Available for both single and double universal joints, bellows are used to cover and protect the joints. Available to protect joints up to 58mm outside diameter.

wixroyd.com

#### Telescopic Universal Joints

Two universal joints connected by a sliding splined shaft with the ability to extend, allowing adjustments in length during installation. Bore diameters 10mm up to 30mm.



2



# **Universal Joints**

Materials Handling

When one single joint is coupled with two shafts (of which the driving one is rotating at a constant speed) forming an angle, a periodic variation of the driven shaft is caused with exactly four fluctuations per revolution.

The difference between the maximum and the minimum speed of the driven shaft depends on the angle formed by the two shafts. The difference grows with the an increase of the angle a°. To have a homokinetic transmission, either two opposite single joints (ensuing that that the two central yokes lie on the same plane and the angles are equal) or a double joint need to be fitted. The irregularity caused by the former articulation is cancelled by the latter. The overall length resulting from the coupling of the two single joints can be reduced by using a double joint. In other words, the double joint is to be considered as the shortest homokinetic transmission.

For low speed applications (Max. 1000 rpm), joints with plain bearings (rubbing bearings) are suggested. They are able to support shock loads, motion reversals, irregular runnings and relatively high torgues. The working angles must be be restricted when using at speeds between 500 - 1000 rpm. Please consult our technical department if you have such an application.

For high rotation speeds, relatively low torgues or wide angles, joints with needle roller bearings are preferred. They can reach 4000 RPM dependent on the angle.





#### To obtain a uniform rotary motion always use either two opposite single joints or one double joints. $\alpha_1 = \alpha_2$ .



When using two opposite single joints ensure the alignment of the inside yokes.



It is essential that the two bending angles a° are equal.



### **Dynamic basic load** ratings of plain bearing rod ends

The pillow block supports should be positioned as close as possible to the joints.



In extensible transmissions make sure that the arrows are perfectly aligned.



ΊΧΓΟι

UNIVERSAL JOINT



### How to read diagrams

The joint capacity to transmit a regular torque at a constant load with no shocks, for a long period, mainly depends on the number of revolutions per minute and the inclination angle a° of the two axes. The diagrams on the following pages are based on this. Each curve corresponds to the joint size (outside diameter "D") and represents the torque that the joint can transmit depending on speed and working angle a°.

The diagrams can be directly read if angle (a°) is 10°. For wider angles, torques are reduced, therefore these are to be corrected using the correction vales (F) relating to the angle shown in the table.

Important Note: Diagrams' values are merely indicative and refer to the single joints only. When choosing a double joint, you have to consider that they can transmit a torque about 10% lower than the same sized single joints. Each application has its own particular motion characteristics, such as: shock loads, motion reversals, connected masses, kind of starting, presence of elastic joints, stops and starts, etc., that have to be considered when choosing the joint.

Working angle a°	Correction value F
5°	1,25
10°	1,00
15°	0,80
20°	0,65
25°	0,55
30°	0,45
35°	0,38
40°	0,30
45°	0,25

#### Example

Known: Power = 0,65 kW RPM = 230

With working angle a 10°, F = 1, we get point P. Torque = 27 Nm corresponding to joint size "D" = 25/26mm = Types 65170.W0016 and 65172.W0012

With working angle a 30°, F = 0,45 (kW 0,65: 0,45 = 1,44 kW) we get point Torque = 60 Nm corresponding to joint size "D" = 32mm = Types 65170.W0020 and 65172.W0016

#### Consider that:

Torque in Nm = 9550 x Power (kW) RPM Torque in Nm = 7020 x Power (HP)

1 kW = 1,35 HP 1 HP = 0,736 kW 1 Kgm = 9,81 Nm 1 Nm = 0,102 Kgm

