


Free Running Safety Clamping Lever,

free-running when not engaged







74860

Material

Plastic technopolymer (polyamide PA) glass fibre reinforced, black. Inner parts: steel, blackened embedded in black plastic.

Tips Unique Safety Handle. When not in use, the lever is not engaged with threaded insert, i.e. the adjustable lever turns freely.

As soon as the lever hub is pushed down, both serrations will engage, allowing the fixture to be released or clamped. After "releasing", the lever disengages through spring tension.

Important Notes

Used where accidental loosening or readjustment can result in accidents.
Temperature resistant to +130°c.

Order No.	I_1	d_1	d_2	d ₃	h_1	h ₂	h ₃	h ₄ stroke	t min.	Weight
74860.W0041	44	M 4	12	15.5	29	9	36	3.5	10	14
74860.W0042	44	M 5	12	15.5	29	9	36	3.5	10	13
74860.W0043	44	M 6	12	15.5	29	9	36	3.5	10	12
74860.W0061	63	M 6	15	19.0	37	12	48	4.0	13	25
74860.W0062	63	M 8	15	19.0	37	12	48	4.0	13	24

