


Combi Pneumatic Toggle Clamp with horizontal cylinder attachment

Pneumatic Toggle Clamps





47030

Material

Body: steel, zinc plated and galvanised. Bushes: case hardened and greased. Rivets: stainless steel.

Complete with tempered, galvanized clamping screw.

Technical Notes

Bearings are pre-lubricated. Clamp ready for installation and consists of:

- vertical toggle clamp no. 40000 (without handle)
- FESTO-pneumatic cylinder, double acting. With magnetic piston for limit position

 F_3 and F_4 = max. clamping force at 6 bar. Vn = air consumption per double stroke in dm³ at 6 bar. Suitable proximity switches for endposition monitoring are available using order 45001. 0.3m PUR cable with M8 connector and rotatable knurled nuts. Switching function: NOC. Output: PNP.

Tips

The console is self-supporting and must be clear of other surfaces. There is a valve for controlling the speed of operation.

Order No.	Size	F ₁ /F ₂ kN	F ₃ kN	F ₄ kN	F ₅ kN	Piston dia	. d ₁	d_2	d_3	h_1	h ₂	h ₃ min.	h ₃ h max.	4 Weight
47030.W0001	1	1	0.3	0.1	0.3	25	5.5	10	M 5	68	36.0	25	32 2	2 770
47030.W0002	2	2	0.5	0.3	0.4	32	6.5	12	G1/8	88	46.0	30	40 2	8 1450
47030.W0003	3	3	0.7	0.4	0.8	40	8.5	16	G1/8	106	55.5	40	50 3	4 3050
Order No.	h ₅	I_1	l ₂	l ₃	I ₄	I ₅	l ₆ min.	l ₆ max.	I ₇	l ₈	Vn dm ³	w_1	w_2	w ₃
47030.W0001	12	225	55	40	33	15	5	10	7.5	0.5	0.3	53	34,5-3	9,5 17.0
47030.W0002	16	305	75	50	56	32	10	20	12.5	10.5	0.4	75	55.0	19.5
47030.W0003	20	370	90	50	74	37	20	30	20.0	14.0	0.8	96	70.0	29.0

