
Drawer Slide - Full Extension

lever disconnect - self-closing - 30 Kg load per pair

Full Extension



Material

Cold rolled steel, zinc plated.

Technical Notes

Self-closing (via dual spring) - toward end of slide closing stroke, pulls draw into fully closed position. Hold-in detent when slide closed. Positive stop. Rails can be disconnected via pressing disconnect lever.

These slides have been tested to 80,000 usage cycles.

Important Notes

Load capacity is static load per pair, at the centre of the rails using all mounting holes. **Sold individually as single slides.**

Order No.	Slide length sl	Slide travel tr	С	е	d	f	g	h	i	Load/pair	Weight
										kg	g
										max.	
P4050.AC0200	200	200	-	-	-	-	-	-	65	30	200
P4050.AC0250	250	254	-	-	-	-	-	-	96	30	250
P4050.AC0300	300	305	-	-	-	172	-	-	160	30	300
P4050.AC0350	350	356	128	-	-	222	128	-	224	30	350
P4050.AC0400	400	406	128	-	-	272	128	-	256	30	400
P4050.AC0450	450	457	128	320	-	322	128	-	320	30	480
P4050.AC0500	500	508	128	352	192	422	128	288	352	30	550
P4050.AC0550	550	559	128	410	224	472	128	282	410	30	625
P4050.AC0600	600	610	128	416	224	522	128	320	448	30	650





P2000 - P7200 Drawer Slides

Drawer Slides technical information



Weight capacity	Weight capacity/pair Kg - is the static load per pair of drawer slides, measured at the centre of a pair of slides, side mounted, spaced 450mm apart, and is based on use of all fixing points on the slide.								
	Important Note: Flat mounting of drawer slides, as opposed to the standard side mounding of slides, is not recommended as it results in a greatly reduced load capacity equal to only 25% of the stated weight capacity.								
Drawer slide terms	Slide length (sl) The longest dimension of a fully closed slide, this should not exceed the depth of cabinet in which slide is installed.								
	Slide travel (tr)	r) Distance a drawer slide moves from fully closed position. (slide length + slide travel = fully extended slide length).							
		a							
		b	75%						
	Full extension	This type of drawer slide can be exter most 3 piece drawer slides. ⓐ	nded 100% of slide length, this is standard for						
	3/4 extension	3/4 extension This type of drawer slide extends to approx. 75% of the slide length, this is standard for most 2 piece drawer slides.							
	Positive stop	Drawer stops at extended/open posit	ion but does not lock or detent.						
	Positive lock	Drawer is released by depressing a lever and pushing drawer inward. From the extended/ open position the same slide may be disconnected by depressing the lever and pulling the drawer out. Hold-in detent Drawer is firmly held in closed position, and released by pulling drawer open (also known as positive catch). Lever disconnect From the extended/open position the slide may be disconnected by depressing lever and pulling drawer out.							
	Hold-in detent								
	Lever disconnect								
	Self-closing	Toward end of drawer slide closing st closed position.							
	Soft self-closing	Toward end of drawer slide closing st drawn into fully closed position.	roke, slide movement is slowed and then						
Side mounting tolerances		e recommend a side space equal to s with an additional 0,2 to 0,5 mm oning.	side space						
	can result in poor	s than 0,2 mm side tolerance running of the drawer slide and de - the same is true if tolerances sed.	side space = nominal slide thickness +0.2 to +0.5mm						
		nclosure faces are square and nounting of the drawer slides.	slide thickness						



wixroyd.com



Wixroyd Drawer Slides

Drawer Slides

product selection charts

