




# Thread Adapter for male lifting points

# Lifting Points & Shackles



## 63302

LIFTING POINTS & SHACKLES

### Material

High tensile steel, strength class >8.

### Technical Notes

The internal portion of the adaptor can be machined (by us) to suit the required lifting bolt thread. Allowing differing sized

lifting bolts to be used.

XX - Advise the internal thread size and pitch required e.g.

63020.W0030 - M20x2,5.

Female thread tolerances required to be 6H (metric) or UNC-2B (inch).

### Tips

Not suitable/rated for customers to machine internal threads themselves.

Only to be used with lifting bolts 63020 to 63150.

Order No.	d <sub>2</sub> tol. 6g (tol. 2A)	d <sub>1</sub> mm max.	d <sub>1</sub> inch max.	l <sub>1</sub>	h <sub>1</sub>	A/F	Torque to Nm (ft-lb)
63302.W0024-xx	M24 x 3,0	18	5/8"	36	10	50	160
63302.W0030-xx	M30 x 3,5	20	7/8"	45	10	50	250
63302.W0036-xx	M36 x 4,0	27	1"	54	10	65	320
63302.W0040-xx	M42 x 4,5	33	1" 1/4	63	10	75	400
63302.W0048-xx	M48 x 5,0	39	1" 1/2	68	10	75	600
63302.W0056-xx	M56 x 5,5	42	1" 3/4	78	10	95	600
63302.W0064-xx	M64 x 6,0	52	2"	90	10	95	600
63302.W0100-xx	M100 x 6,0	80	3" 1/2	100	15	155	600
63302.W5088-xx	UNC 7/8"-9	16	5/8"	33	10	50	(100)
63302.W5100-xx	UNC 1"-8	18	3/4"	36	10	50	(125)
63302.W5125-xx	UNC 1" 1/4-7	24	7/8"	45	10	50	(200)
63302.W5138-xx	UNC 1" 3/8-6	27	1"	54	10	65	(300)
63302.W5150-xx	UNC 1" 1/2-6	30	1" 1/8	61	10	75	(300)
63302.W5200-xx	UNC 2"-4 1/2	39	1" 1/2	76	10	95	(450)
63302.W5275-xx	UNC 2" 3/4-4	56	2" 1/4	105	10	155	(600)
63302.W5400-xx	UNC 4"-4	80	3" 1/4	150	15	155	(800)