




# Swing Handles - with Rod Control

40mm euro cylinder lock - padlockable - zinc or

## Swing Handles



**B2088**

SWING HANDLES

### Material

**Type One:** Body & Handle: die cast zinc, black powder coated.

**Type Two:** Body: Polyamide PA6, black. Handle: die cast zinc, black powder coated.

Cylinder lock: die cast zinc, chrome plated.

Rod Control Mechanism: die cast zinc.

**Supplied with:** Keys: two per lock.

**Not supplied:** Cam: order separately.

### Technical Notes

Order cam separately.

**Cams:** see suitable cam A0215. Select

„without projection“ cam type.

Dimensions ch and cl relate to cam. Use formula to calculate ch (required cam off-set), and refer to cam selection chart;

**ch = h - lh** where;

**ch** = required cam off-set/height.

**h** = grip length (distance between inside of latch face and front of cam).

**lh** = body length of cam latch/lock to be used (see product table below).

**Rods & Guides:** to achieve 3-point latching - A0303, A0321, A0325.

### Tips

90° degree handle rotation combines with rod latch to open or close. All die cast metal construction provides higher strength than standard models. Ideal for electrical cabinets, telecom racks or enclosures max. panel thickness of 1 to 4mm. For use inside of cabinet gasket. Universal left/right.

Order No.	Body	Handle	Lock type	Key type	l	Padlockable	w	lh	a	b	dm stroke
<b>B2088.AW0010</b>	Zinc	Zinc	40 Euro	Keyed Alike	160	No	34	23	122	196	15
<b>B2088.AW0310</b>	Polyamide	Zinc	40 Euro	Keyed Alike	160	No	34	23	122	196	15
<b>B2088.AW0020</b>	Zinc	Zinc	40 Euro	Keyed Alike	160	Yes	34	23	122	196	15
<b>B2088.AW0320</b>	Polyamide	Zinc	40 Euro	Keyed Alike	160	Yes	34	23	122	196	15