


Quick Release Ball JointsA2 stainless and steel, zinc-plated





65542

Material

Body: stainless steel (A2, AISI 303) or steel zinc-plated.

Shield and ball stud: carbon steel. Body and ball stud: case hardened. Spring: (302 S26) stainless steel or equivalent, zinc plated.

Technical Notes

The spring loaded outer shield allows both rapid release and reconnection of the ball stud.


Linkage assemblies can be installed or removed without disturbing pre-set centres.

These are metric equivalents to SAE J 490 Style 1 quick release detachable ball joints.

Tips

Standard thread is a right hand thread.

Order No.	Thread hand	d_1	d_2	I_1	I ₂	d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	l ₃	A/F	Weight g
65542.W0105	Right	6.35	M 5	23.0	28	7.9	11.1	4.35	11.1	11.9	28.6	11.1	8	17
65542.W0106	Right	7.9	M 6	24.6	30	9.4	13.0	4.95	12.6	12.6	33.4	13.0	10	25
65542.W0108	Right	8.6	M 8	31.7	40	11.1	16.0	5.8	15.2	15.2	40.6	14.3	11	48
65542.W0110	Right	10.7	M10	39.7	49	14.1	19.0	6.85	19.8	19.8	51.4	27.0	13	78






Quick Plug Couplings with radial offset compensation



UPLING



64500



Material

Body: steel, heat-treated, phosphated. Lock nut: steel, blackened (ISO 4035/8675).

Technical Notes

For quick coupling/uncoupling of components within a linear movement application, with the additional advantage

of compensating for radial off-set between the components. In built adjustment feature of the quick plug coupling means manual adjustment of the coupled units is unnecessary. Coupling via means of a t-slot channel within the coupling nut.

Tips

Can be linked to pneumatic and hydraulic

lifting cylinders in many different applications.


Important note: suitable for linear movement applications, does not transmit any torque.

Order No.	Coupling Type	d_1	d ₂	d ₃	₁ ≈	l ₂ min.	l ₃	l ₄ min.	l ₅	Tensile & compression load kN max.	A/F ₁	A/F ₂	Axial offset x max.	Weight g
64500.W0006	Screw	M_6	21,0		37,5	11,0	14	9,0	18,0	2,5	19	10	0,6	44
64500.W0008	Screw	M_8	26,0		45,0	13,5	17	11,5	22,5	4,5	24	13	0,7	86
64500.W0010	Screw	M10	30,0		56,2	16,0	20	16,0	29,0	6,5	27	17	0,7	147
64500.W0012	Screw	M12	32,5		66,7	21,0	25	17,0	34,0	10,0	30	19	0,8	208
64500.W0016	Screw	M16	39,0		83,0	25,0	30	23,0	42,0	18,0	36	24	1,0	383
64500.W0020	Screw	M20	44,0		93,5	29,0	35	23,5	45,5	30,0	41	30	1,0	571
64500.W0030	Screw	M10 x 1,25	30,0		56,2	16,0	20	16,0	29,0	6,5	27	17	0,7	147
64500.W0032	Screw	M12 x 1,25	32,5		66,7	21,0	25	17,0	34,0	10,0	30	19	0,8	207
64500.W0036	Screw	M16 x 1,50	39,0		83,0	25,0	30	23,0	42,0	18,0	36	24	1,0	384
64500.W0040	Screw	M20 x 1,50	44,0		93,5	29,0	35	23,5	45,5	30,0	41	30	1,0	576
64500.W0056	Nut	M_6	21,0	11,0	37,5	11,0		9,0	18,0	2,5	19	10	0,6	47
64500.W0058	Nut	M_8	26,0	14,4	45,0	13,5		11,5	22,5	4,0	24	13	0,7	91
64500.W0060	Nut	M10	30,0	19,0	56,2	15,0		16,0	29,0	6,5	27	17	0,7	160
64500.W0062	Nut	M12	32,5	21,2	66,7	17,5		17,0	34,0	10,0	30	19	0,8	223
64500.W0066	Nut	M16	39,0	27,0	83,0	22,0		23,0	42,0	18,0	36	24	1,0	401
64500.W0070	Nut	M20	44,0	34,0	93,5	25,0		23,5	45,5	30,0	41	30	1,0	606
64500.W0080	Nut	M10 x 1,25	30,0	19,0	56,2	15,0		16,0	29,0	6,5	27	17	0,7	159
64500.W0082	Nut	M12 x 1,25	32,5	21,2	66,7	17,5		17,0	34,0	10,0	30	19	0,8	221
64500.W0086	Nut	M16 x 1,50	39,0	27,0	83,0	22,0		23,0	42,0	18,0	36	24	1,0	400
64500.W0090	Nut	M20 x 1,50	44,0	34,0	93,5	25,0		23,5	45,5	30,0	41	30	1,0	601



Quick Plug Couplings with radial offset compensation












64600



Material

Body: steel, heat-treated, tempered, phosphated.

Lock nut: steel, blackened (ISO 4035/8675).

Technical Notes

For quick coupling/uncoupling of components within a linear movement application, with the additional advantage

of compensating for radial off-set between the components. In built adjustment feature of the quick plug coupling means manual adjustment of the coupled units is unnecessary. Coupling via means of a t-slot channel within the coupling nut.

*kN max is the maximum tensile and compression load.

Tips

Ideal quick coupler where space is limited. Can be linked to pneumatic and hydraulic lifting cylinders in many different applications.

Important note: suitable for linear movement applications, does not transmit any torque.


Order No.	Coupli	ng Type		d_1	d	2	d ₃	d_4		d ₅	Weight
											g
64600.W0206		rew		M_6	4:		-	5.5		10	75
64600.W0208		rew		M_8	4		-	6.6		11	116
64600.W0210		rew		M10	5		-	6.6		11	175
64600.W0212	Sc	rew		M12	5		-	6.6		11	281
64600.W0216	Sc	rew		M16	6	5	-	9.0		15	458
4600.W0220	Sc	rew		M20	80)	-	11.0		18	817
4600.W0230	Sc	rew	N	110x1,25	50	C	-	6.6		11	176
64600.W0232	Sc	rew	N	112x1,25	5	5	-	6.6		11	280
54600.W0236	Sc	rew	M	116x1,50	6	5	-	9.0		15	454
64600.W0240	Sc	rew	N	120x1,50	8)	-	11.0		18	850
54600.W0256	N	lut		M_6	4:	2	11.0	5.5		10	77
54600.W0258	N	lut		M_8	48	3	14.4	6.6		11	123
54600.W0260	N	lut		M10	50	C	19.0	6.6		11	187
54600.W0262	N	lut		M12	5	5	21.2	6.6		11	295
54600.W0266	N	lut		M16	6	5	27.0	9.0		15	472
54600.W0270	N	lut		M20	8)	34.0	11.0		18	849
54600.W0280	N	lut	N	110x1,25	50	O	19.0	6.6		11	187
64600.W0282	N	lut	N	112x1,25	5	5	21.2	6.6		11	298
64600.W0286	N	lut	N	116x1,50	6	5	27.0	9.0		15	477
64600.W0290	N	lut	N	120x1,50	80)	34.0	11.0		18	852
											kľ
Order No.	₁ ≈	l ₂ min.	l ₃	I ₄	I ₅	I ₆	I ₇	A/F	t	Axial offset x max.	k ki ma
64600.W0206	30.5	11.0	14	3.0	11.0	7.0	14.0	10	5.4	0.6	2
64600.W0208	35.5	13.5	17	3.0	13.0	8.0	16.0	13	6.4	0.7	4
64600.W0210	43.2	16.0	20	4.2	16.0	9.0	17.0	17	6.4	0.7	6.





Quick Plug Couplings with radial offset compensation and screwed flange

Order No.	₁ ≈	l ₂ min.	l ₃	I ₄	I ₅	I ₆	I ₇	A/F	t	Axial offset x max.	kN kN max.
64600.W0212	53.2	21.0	25	4.2	20.5	10.0	19.0	19	6.4	0.8	10.0
64600.W0216	64.0	25.0	30	5.0	23.0	12.5	22.5	24	8.5	1.0	18.0
64600.W0220	74.0	29.0	35	5.0	26.0	17.0	28.0	30	10.4	1.0	30.0
64600.W0230	43.2	16.0	20	4.2	16.0	9.0	17.0	17	6.4	0.7	6.5
64600.W0232	53.2	21.0	25	4.2	20.5	10.0	19.0	19	6.4	0.8	10.0
64600.W0236	64.0	25.0	30	5.0	23.0	12.5	22.5	24	8.5	1.0	18.0
64600.W0240	74.0	29.0	35	5.0	26.0	17.0	28.0	30	10.0	1.0	30.0
64600.W0256	30.5	11.0	-	3.0	11.0	7.0	14.0	10	5.4	0.6	2.5
64600.W0258	35.5	13.5	-	3.0	13.0	8.0	16.0	13	6.4	0.7	4.5
64600.W0260	43.2	15.0	-	4.2	16.0	9.0	17.0	17	6.4	0.7	6.5
64600.W0262	53.2	17.5	-	4.2	20.5	10.0	19.0	19	6.4	0.8	10.0
64600.W0266	64.0	22.0	-	5.0	23.0	12.5	22.5	24	8.5	1.0	18.0
64600.W0270	74.0	25.0	-	5.0	26.0	17.0	28.0	30	10.0	1.0	30.0
64600.W0280	43.2	15.0	-	4.2	16.0	9.0	17.0	17	6.4	0.7	6.5
64600.W0282	53.2	17.5	-	4.2	20.5	10.0	19.0	19	6.4	0.8	10.0
64600.W0286	64.0	22.0	-	5.0	23.0	12.5	22.5	24	8.5	1.0	18.0
64600.W0290	74.0	25.0	-	5.0	26.0	17.0	28.0	30	10.0	1.0	30.0






Quick Plug Couplings

with angular radial offset compensation





64700



Material

Body: steel, heat-treated, tempered, phosphated.

Nut: steel, heat-treated, phosphated. Spring: stainless steel.

Coupling part: steel, heat-treated, nitrided, blackened.

Lock nut: steel, blackened (ISO 4035/8675).

Technical Notes

Compensates for both radial off-set and

angular off-set between the components, making it ideal for applications with non-aligned linear components. Inbuilt adjustment feature of the quick plug coupling means manual adjustment of the coupled units is unnecessary. Coupling via means of a t-slot channel within the coupling nut.

Tips

Solid and compact design, no loose elements. Can be linked to pneumatic and hydraulic lifting cylinders in many different

applications.

Important note: suitable for linear movement applications, does not transmit any torque.


Order No.	d_1	d_2	d ₃	₁ ≈	I ₂	I ₃	Weight g
64700.W0406	M 6	24.5	9.6	52	14	9.5	75
64700.W0408	M 8	30.0	15.0	63	18	11.5	137
64700.W0410	M10	44.0	21.0	81	22	16.0	401
64700.W0412	M12	44.0	21.0	85	26	16.0	405
64700.W0416	M16	60.0	32.0	121	34	26.0	1127
64700.W0420	M20	60.0	32.0	129	42	26.0	1152
64700.W0430	M10x1,25	44.0	21.0	81	22	16.0	403
64700.W0432	M12x1,25	44.0	21.0	85	26	16.0	406
64700.W0436	M16x1,50	60.0	32.0	121	34	26.0	1128
64700.W0440	M20x1,50	60.0	32.0	129	42	26.0	1155

Order No.	l ₄ min.	I ₅	I ₆	Radial offset compensation max.	Tensile load kN max.	A/F ₁	A/F ₂	A/F ₃	A/F ₄
64700.W0406	13	29	18.5	0.6	2.5	22	19	8	5
64700.W0408	16	33	23.5	0.6	4.5	27	24	13	7
64700.W0410	24	43	30.5	0.7	6.5	41	36	18	12
64700.W0412	24	43	34.5	0.7	10.0	41	36	18	12
64700.W0416	34	62	45.0	1.0	18.0	55	46	27	18
64700.W0420	34	62	53.0	1.0	30.0	55	46	27	18
64700.W0430	24	43	30.5	0.7	6.5	41	36	18	12
64700.W0432	24	43	34.5	0.7	10.0	41	36	18	12
64700.W0436	34	62	45.0	1.0	18.0	55	46	27	18
64700.W0440	34	62	53.0	1.0	30.0	55	46	27	18



Quick Plug Couplings with angular radial offset compensation








Quick Plug Coupling - Cam Locking



UPLING



64775



Material

Body: steel S45C, nickel plated. Pin and Spring: stainless steel, SUS304

Technical Notes

For quick coupling/uncoupling of components within a linear movement application. Coupling via means of a 90°C turn of coupling into the cam locking receiver. Please order receivers separately, see part nos. 64780 and 64782. Temperature resistant to 200°C

Tips

Can be linked to pneumatic and hydraulic

lifting cylinders in many different applications.

Important Notes

Suitable only for linear movement applications, does not transmit any torque.

Actuation

- Following installation dimensions for both coupling and receiver in introductory
- Once coupling and receiver are correctly installed, align male coupling to female receiver, paying attention to correctly


alight pins on the coupling's shaft to holes in receiver.

- Engage coupling and receiver, to lock turn shaft or block 90 degrees to clamp.
- When properly locked an audible "click" is heard.
- When properly installed, repeatability of upto +/- 0.08mm is achievable.
- To release, reverse steps described above.

Order No.	d ₁ -0.04 -0.08	d ₂ -0.04 -0.08	d ₃	h_1	h ₂	I_1	Shear strength N	Tensile strength N	Clamping force N	Weight g
64775.W0514	5	14	3	23.5	20	9.5	1800	1200	max. 30	25

Receiver - Shaft Mount - Cam Locking for Quick Plug Coupling no. 64775







64780

Material

Body: tempered steel SCM440, nickel plated.

Technical Notes

Receiver for use with quick plug coupling,

cam locking no. 64775. Shaft mount version suited to installation on shafts; such as the end of pneumatic or hydraulic cylinders.

Temperature resistant to 200° C

Important Notes

Suitable only for linear movement applications, does not transmit any torque.

Order No. 64780.W0514

+0.08|+0.04 5 d₂ tol. h9 14 d₃

h₁
14.5


h₂

Weight g 10




Operating Principle


When the male quick plug coupling is fully inserted into the receiver and actuated, the internal spring is compressed to clamp the shaft.



Operating Instructions


- 1 Insert the shaft into the keyway of cam receiver.
- 2 Rotate the shaft block 90° to clamp the element. An audible click can be heard when clamped. For unclamping, reverse these steps.





Operating Dimensions

How to mount shaft coupling clamp







Quick Plug Coupling - Cam Locking

overview

Materials Handling




How to mount receiver (shaft mount)



How to mount receiver (plate mount)

Repeatability

ov-W64775-A-T-W64780-A-T-b-rnh- Updated -31-10-2022



Prepare male and female fittings for highly accurate locating. Repeatability of ±0.08 is achievable.




Quick Plug Coupling - Cam Locking

overview




Applications

Changes of thrust pads




Changes of riser



Notes


Pay attention to the direction of holes for spring pins.





Receiver - Plate Mount - Cam Locking for Quick Plug Coupling no. 64775







64782

Material

Body: tempered steel SCM440, nickel plated.

Technical Notes

Receiver for use with quick plug coupling,

cam locking no. 64775. Plate mount version suited to installation in thin walled parts, and sub-flush to the mounting surface.

Temperature resistant to 200° C

Suitable only for linear movement applications, does not transmit any torque.

Order No.		d ₂	d_3	d_4	h_1	h_2	h ₃	w_1	W_2	w_3	Weight
	+0.08 +0.04	tol. h9									g
64782.W0514	5	14	13	2.4	8	2	1.5	17	21	25	8

