



10020

STANDARD MANUAL CLAMPING

Material

Steel, heat-treated and enamelled.

14000).

collar nuts, 25000 plain washer.

Technical Notes

To be used with step blocks etc (part no.

Tips

Used with:

21000 T-slot bolts, 24000 T-nuts, 24400

Order No.	For bolt	For bolt inch	l_1	l_2	l_3	w_1	w_2	w_3	h_1	Weight g
10020.W0007	M 6	1/4"	50	20	10	20	6.6	8	10	55
10020.W0008	M 6	1/4"	80	45	10	20	6.6	8	10	90
10020.W0009	M 8	5/16"	60	22	13	25	9.0	10	12	100
10020.W0010	M 8	5/16"	100	60	13	25	9.0	10	12	180
10020.W0011	M10	3/8"	80	30	15	30	11.0	12	15	200
10020.W0012	M10	3/8"	125	70	15	30	11.0	12	15	350
10020.W0014	M12, M14	1/2"	100	40	21	40	14.0	14	20	450
10020.W0015	M12, M14	1/2"	160	90	21	40	14.0	14	20	770
10020.W0018	M16, M18	5/8"	125	45	26	50	18.0	18	25	900
10020.W0019	M16, M18	5/8"	200	110	26	50	18.0	18	25	1500
10020.W0022	M20, M22	3/4"	160	60	30	60	22.0	22	30	1700
10020.W0026	M24	1"	200	80	35	70	26.0	26	30	2500

